

Capacitor, Ceramic, SMD, MLCC, High Temp, Ultra-Stable, Low Loss, 5600 pF, +/-5% Tol, 2000 V, COG, 2824



General Information	
Supplier:	KEMET
Application:	200C
Chip Size:	2824
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, High Temp, Ultra-Stable, Low Loss
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.1	+/-0.4
W	6.1	+/-0.4
T	2.5	+/-0.20
B	0.76	+/-0.4

Specifications	
Capacitance:	5600 pF
Voltage:	2000 V
Tolerance:	+/-5%
Temperature Range:	-55/+200C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	2400 V

Packaging Specifications	
Package Kind:	Cut Reel
Package Quantity:	50