



GREENLEE.
A Textron Company

MADE FOR THE TRADE!™



PUNCH UNIT-CONNECTOR 25 PIN RS-232

Electronic Connector Panel Punches

Cat No: 50344200

UPC No: 783310344209

Description

- Cut-out and mounting slots are punched in one operation
- Drill only one 7/16 IN (11.1 mm) pilot hole. (use with Kwik Stepper® step bits.)
- Fast, accurate panel punching with no sawing or filing required
- Universal size punches for front or back mount of TRW Cinch and ITT Cannon-type or equivalent connectors in 9, 15, 25, 37 or 50-pin configurations
- U.S. Patent No. 4,899,447

Specifications

- Capacity :
 - 16 GA (1.500 MM) Mild Steel
 - 10 GA (3.500 MM) Aluminum
- No. Of Pins : 25
- Operation Type :
 - Manual with Wrench
 - Quick Draw® And Quick Draw 90® Hydraulic Drivers, Battery Driver, Ram And Pump Hydraulic Drivers Aluminum
- Replacement Part : 34418 Punch, 35198 Die Unit, 34421 Draw Stud, 04638 Square Counter Nut, 34733 Drive Nut
- Size : 1.655 IN X 1.853 IN X 0.469 IN (42.000 MM X 47.100 MM X 11.900 MM)
- Type : Electronic Connector Panel
- Weight : 2.000 LB (0.910 KG)