

## 2-conductor ground terminal block; suitable for Ex e II applications

Item No.: 2010-1207



2-conductor ground terminal block; suitable for Ex e II applications

### Marking

RoHS ✓  
Compliant

### Business data

Supplier	WAGO
Item no.	2010-1207
GTIN / EAN	4017332076180
Content	1
Order amount	25
Customer item number	

### Notes



### Technical data


#### Miscellaneous

Total number of connection points	2
Total number of potentials	1
Color	green-yellow
Ratings according to 1	IEC/EN 60947-7-2
Connection technology (1)	Push-in CAGE CLAMP®
Nominal cross section 1	10 mm <sup>2</sup>
Solid sizes 1	0.5 ... 16 mm <sup>2</sup> / 20 ... 6 AWG
solid, directly pluggable 1	2.5 ... 16 mm <sup>2</sup> / 14 ... 6 AWG
Fine-stranded wires 1	0.5 ... 16 mm <sup>2</sup> / 20 ... 6 AWG
min. fine-stranded with insulated ferrule, push-in terminati	2.5 mm <sup>2</sup> / 14 AWG

<b>Technical data</b>	
<i>Strip length 1</i>	<i>17 ... 19 mm / 0.67 ... 0.75 in</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Design</i>	<i>horizontal</i>
<i>Marking level</i>	<i>Center/Side marking</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Fire load [MJ]</i>	<i>0.273 [MJ]</i>
<i>Weight [g]</i>	<i>30.1 [g]</i>
<i>Width</i>	<i>10 mm / 0.394 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>36.9 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>36.9 mm / 1.453 in</i>
<i>Length</i>	<i>67.8 mm / 2.669 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>

Images & drawings





#### Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.