



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



KIT PREMISE SERVICE KIT PREMISE SERVICE

Premise Service Kit

Cat No: 52050389

UPC No: 769328108156

### Description

---

Our biggest data, voice, and coaxial LAN installation kit provides everything for twisted pair and coaxial cable installation. All tools contained in a professional blow-mold case complete with form-fitting foam.

## Specifications

---

- Includes :
- PA91179 KT8 Round Cable Cutter
- PA1257 LC-CST CATV "F" Coax Stripper
- PA1116 Data SureStrip® UTP/STP And Flat Satin Cutter/Stripper
- PA8000 CrimpALL® Crimp Frame with EZI-CHANGE™ Thumb Screws
- PA3589 SurePunch® Pro Punchdown Tool
- PA4599 SurePunch® Pro Detachable LED light
- PA4578 110 blade
- PA4573 66 blade
- PA1543 LAN ProNavigator® UTP/STP continuity tester & remote
- PA1573 Telephone Test Set & LAN Cable-Check™
- PA1902 RJ45 8-way adapter
- Die Sets:
- PA2062 RJ11/12 WE/SS-style
- PA2687 RJ45 WE/SS-style & RG6/RG6 QS CATV "F"
- Replacement Part :
- PA91179 KT8 Round Cable Cutter
- PA1257 LC-CST CATV "F" Coax Stripper
- PA1116 Data SureStrip® UTP/STP And Flat Satin Cutter/Stripper
- PA8000 CrimpALL® Crimp Frame with EZI-CHANGE™ Thumb Screws
- PA3589 SurePunch® Pro Punchdown Tool
- PA4599 SurePunch® Pro Detachable LED light
- PA4578 110 blade
- PA4573 66 blade
- PA1543 LAN ProNavigator® UTP/STP continuity tester & remote
- PA1573 Telephone Test Set & LAN Cable-Check™
- PA1902 RJ45 8-way adapter
- Die Sets:
- PA2062 RJ11/12 WE/SS-style
- PA2687 RJ45 WE/SS-style & RG6/RG6 QS CATV "F"
- Size : 17.000 IN (432.000 MM) Width x 13.400 IN (341.000 MM) Length x 4.500 IN (115.000 MM) Depth
- Type : Premise
- Weight : 7.600 LB (3.500 KG)