

KEMET Part Number: C1210X106M3RACTU
(C1210X106M3RAC7800)

Capacitor, Ceramic, SMD, MLCC, FT-CAP, Temp Stable, 10 uF, +/-20% Tol, 25 V, X7R, 1210 (3225 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	1210 (3225 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, FT-CAP, Temp Stable
Termination Type:	Flexible Termination
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.3	+/-0.4
W	2.6	+/-0.3
T	2.5	+/-0.30
B	0.6	+/-0.25

Specifications	
Capacitance:	10 uF
Voltage:	25 V
Tolerance:	+/-20%
Temperature Range:	-55/+125C
Dissipation Factor:	3.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	50 MOhm
Dielectric Strength:	62.5 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	1000