

KEMET Part Number: C0402C183K3NACTU
(C0402C183K3NAC7867)

Capacitor, Ceramic, SMD, MLCC, High Temperature, Temperature Stable, 0.018 uF, +/-10% Tol, 25 V, X8L, 0402 (1005 metric)



General Information	
Supplier:	KEMET
Application:	Standard Chip
Chip Size:	0402 (1005 metric)
Temperature Coefficient:	X8L
Part Type Description:	SMD, MLCC, High Temperature, Temperature Stable
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1	+/-0.05
W	0.5	+/-0.05
T	0.5	+/-0.05
B	0.3	+/-0.1
S	0.3	MIN

Specifications	
Capacitance:	0.018 uF
Voltage:	25 V
Tolerance:	+/-10%
Temperature Range:	-55/+150C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	10 GOhm
Dielectric Strength:	62.5 V
Miscellaneous:	Note: Referee time for X8L dielectric for this part number is 1000 hours

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Paper Tape
Package Quantity:	10000