

PROLINE G2 MOBILE BASE



APPLICATION

Mobile bases include casters and extend beyond the front and rear of 600- and 800-mm wide modular enclosures to provide enhanced stability.

FEATURES

- The front and rear top surfaces of the base are trimmed with 3-mm thick black rubber mats
- Four non-locking casters provide a maximum load-bearing capacity of 1000 lb. (453.6 kg)

SPECIFICATIONS

- Available as standard product for 600- and 800-mm wide frames
- The base fastens to the underside of the frame and provides integral mounting of furnished casters
- Casters and mounting hardware are furnished
- Exercise care when using casters to move the enclosure
- Avoid tipping and damage to the enclosure and its contents by slowly moving the enclosure on its casters across smooth, flat flooring
- Avoid: large cracks; floor displacement; seams; gravel; and any other obstruction
- Never use casters while transporting an enclosure by truck on roadways
- Contact Hoffman for more information

FINISH

- Polyester powder paint; RAL 7035 textured light gray standard
- Custom colors available


ACCESSORIES

Mobile Base Leveling Kit

BULLETIN: P40

Standard Product

Catalog Number	Fits Frame Nominal W x D
P2BM64	600 x 400
P2BM65	600 x 500
P2BM66	600 x 600
P2BM68	600 x 800
P2BM84	800 x 400
P2BM85	800 x 500
P2BM86	800 x 600
P2BM88	800 x 800
P2BM810	800 x 1000



Model	Component	Type	Width	Depth	Catalog Number
P2	B	M	8	6	P2BM86
PROLINE G2	Base	0 = solid base 0mm 1 = fully sealed plinth P1 = plinth base 100mm P2 = plinth base 200mm GP = gland plate T = transportation base M = mobile base	mm 8 = 800 6 = 600	mm 10 = 1000 8 = 800 6 = 600 5 = 500 4 = 400	

MOBILE BASE LEVELING KIT



Levelers mount in the outer corners of the Mobile Base, providing load-bearing capacity of 1000 lb. (453.6 kg).

BULLETIN: P20

Catalog Number	Description	Use with
PMBLM12	Mobile Base Leveling Kit	Mobile Base