

# ACS-3, ACS-6, ACS-15 & ACS-30

## SCALIX Parts Counting Bench Scales



These parts counting scales are ideal for inventory control, stocktaking and all other counting applications. They are also ideal for standard weighing applications being robust and suited to harsh industrial environments.

- 4 selectable units: Kg, g, lb, oz
- Impact-resistant ABS case with stainless steel pan, adjustable feet and level bubble
- 60mm 3 Line LCD display with backlight for total weight, piece weight and piece count
- Auto-backlight when an item is placed on the weighing pan
- Tare function can be repeated throughout a weighing cycle
- Plus/minus weighing for check weighing applications
- Zero function and stability indicator
- Lack of sample indicator when the sample amount is too low for accurate counting
- Lack of piece weight when the sample unit weight is not heavy enough for accurate operation
- Numerical keypad for count setting by quantity or unit weight
- Parts counting with freely selectable reference quantity of sample pieces
- Accumulation function for adding parts counting results, weighing results, total accumulated weight and number of counts
- Memory function to store and total readings (up to 99 counts)
- Audible alarm when exceeding preset upper and lower quantity limits
- Battery charge condition indicator
- Supplied with internal rechargeable battery mains lead

### Technical Specifications

Model	MACS-3	MACS-6	MACS-15	MACS-30
Capacity	3Kg	6Kg	15Kg	30Kg
Resolution	0.1g	0.5g	1g	1g
Accuracy	±0.2g	±1g	±2g	±2g
Min Pcs Wt	1g	5g	10g	10g
Pan Size	280 x 180mm			
Power	Internal recharging battery mains lead			
Dimensions	300 x 260 x 112mm (unit), 280 x 180mm (pan)			
Weight	3.2Kg with rechargeable battery			