

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0022284060

Status:

Active

Overview:

SPOX™ Wire-to-Board Connectors

Description:

KK® 254 Breakaway Header, Vertical, 6 Circuits, Tin (Sn) Plating, Mating Pin Length 6.09mm

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

LR19980

UL

E29179

General

Product Family

PCB Headers

Series

42375

Application

Board-to-Board, Signal, Wire-to-Board

Overview

SPOX™ Wire-to-Board Connectors

Product Name

KK® 254

UPC

800753684034

Physical

Breakaway

Yes

Circuits (Loaded)

6

Circuits (maximum)

6

Color - Resin

Black

Durability (mating cycles max)

25

First Mate / Last Break

No

Flammability

94V-0

Glow-Wire Compliant

No

Guide to Mating Part

No

Keying to Mating Part

None

Lock to Mating Part

None

Material - Metal

Brass

Material - Plating Mating

Tin

Material - Plating Termination

Tin

Material - Resin

High Temperature Thermoplastic

Net Weight

0.367/g

Number of Rows

1

Orientation

Vertical

PC Tail Length

3.18mm

PCB Locator

No

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Pitch - Mating Interface

2.54mm

Plating min - Mating

2.540µm

Plating min - Termination

2.540µm

Polarized to Mating Part

No

Polarized to PCB

No

Shrouded

No

Stackable

No

Surface Mount Compatible (SMC)

Yes

Temperature Range - Operating

See Product Specification

Termination Interface: Style

Through Hole



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

ED/21/2016 (20 June

2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product

environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any

non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Search Parts in this Series

42375 Series

Mates With

KK® Crimp Housing [2695](#) , [6471](#) , [7880](#) ,

KK® PC Board Connector [4455](#)

Electrical

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V

Solder Process Data

Duration at Max. Process Temperature (seconds)	005
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	235

Material Info

Old Part Number	42375-0006
-----------------	------------

Reference - Drawing Numbers

Sales Drawing	SD-42375-001
---------------	--------------

This document was generated on 07/20/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION