


© COPYRIGHT 1998 BY SPC TECHNOLOGY. ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F004, Total Pages: 2 Effective: 7/15/97, DCP No: 229 Supersedes DCP No: 103					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
3159000	28	T-1 3/4MIDGET GROOVE LAMP	CL	2000.1.24	LEI	2000.1.24	SHIH	2000.1.24
		28V0.04A 0.34CP 4000HRS C-2F						

NOTE:

- LAMPS SHALL BE CAPABLE OF OPERATION AND STORAGE AT TEMPERATURES FROM -40°C TO +85°C WITHOUT DEGRADATION.
- DIMENSIONS ARE IN MILLIMETERS.



SPC-F004.DWG

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

multicomp

T-13/4GB	DRAWN BY:	DATE:	DRAWING TITLE: MCFPM-004					
	CL	2000.1.24	SIZE	DWG. NO.	ELECTRONIC FILE	REV		
	CHECKED BY:	DATE:	5.84X15.9 MAX	OPE. 157. 5. 6 φ GB. (FS) . 4				
	LEI	2000.1.24	SCALE:	U.O.M.:	SHEET:	1	OF 1	
	APPROVED BY:	DATE:						
	SHIH	2000.1.24						