



## UEB220-6U UNCOMMITTED EXTENDER VECTORBORD®



6U Overall 3-row, 96 positions DIN 41612 style Uncommitted Extender (click on image to enlarge)



Shown 96-pin DIN 41612 (rows A, B, C) Connector (click on image to enlarge)

### KEY FEATURES :

- Two Uncommitted Extenders [UEB220-3U](#) attached on top & bottom with mending plate to create [UEB220-6U](#) Extender
- Uncommitted Extenders (Test Adapters) are strictly point-to-point with trace shielding
- Jumpers are provided for interrupting each signal lines
- Mounting pads for additional DIN connector or test points for attachment of test specimens on either side
- Max. current per contact @ nominal 50° C = 1.75A
- Voltage rating 200 RMS or 300 VDC
- Suitable for 160mm or 220mm card depth

### BOARD SPECIFICATIONS :

- Material : FR-4 Epoxy Glass
- PCB UL94V-0, PCB RoHS Compliant
- 6 Internal 1oz. copper layers
- PCB exposed Copper areas plated with Immersion Gold

### MECHANICAL SPECIFICATIONS :

- Combine Board Height 6U ( 9.187" ) ( 233.35mm )
- Each Board Length 11.75" ( 298mm )
- PCB Thickness 0.062" ( 1.6mm )
- Card Extender brackets (arms) on top & bottom (P/N : [5210211](#))
- Expandable Height in multiples of 3U, i.e. 3U, 6U, 9U etc. can be achieved with mending plates
- Mending plates sold separately