



PRODUCT DATA SHEET

KT64DL

MULTIFUNCTION 6-IN-1 TESTER

- Easy to use
- NEW Anti-Trip Technology for full no trip LOOP testing on all RCD types
- Test button in probe as well as lockdown test button for 'hands free' testing
- Easy PFC & PSC measurement without the need to alter test probes
- 250, 500 & 1000V insulation tests with auto discharge
- Additional LED for warning of high voltage output in insulation test mode
- Memory for test lead resistance compensation
- Selectable touch voltage
- Backlit display
- Auto-test memory for RCD testing – single screen results
- End of line calibration certificate included

ACCESSORIES

- ACC064SP G7 Test remote with remote test button
- ACC064 G7 Test lead set
- Kamp 12 Mains lead
- Batteries
- Test lead pouch
- Instruction Manual
- Soft carry case
- Calibration Certificate

OPTIONAL

- FC2000 calibration checker

KT64DL

Multifunction 6-in-1 tester

SPECIFICATIONS

CONTINUITY

Open Circuit Voltage (DC)	Short Circuit Current	Range	Accuracy	
5V±20%	Greater than 200mA	20 / 200 / 2000Ω Auto-Ranging	0 ~ 0.19 Ω	±0.1 Ω ±(2%rdg+8dgt)

2Ω Buzzer: Buzzer sounds when measured 2Ω Buzzer Accuracy: 2Ω±0.3Ω resistance is 2Ω or less.

INSULATION RESISTANCE

Open Circuit Voltage (DC)	Rated Circuit Current	Range	Accuracy
250V+40% -0%	1mA or greater @ 250k Ω	20 / 200MΩ Auto-Ranging	20 ~ 200M Ω ±(5%rdg+6dgt)
500V+30% -0%	1mA or greater @ 500k Ω	20 / 200 / 1000MΩ Auto-Ranging	200 ~ 2000M Ω ±(5%rdg+6dgt)
1000V+20% -0%	1mA or greater @ 1M Ω	20 / 200 / 2000MΩ Auto-Ranging	200 ~ 2000M Ω ±(5%rdg+6dgt)

LOOP IMPEDANCE

Function	Rated Voltage	Nominal Test Current at 0Ω External Loop: Magnitude/Duration	Range	Accuracy
L-PE	100 ~ 260V 50/60Hz	20Ω: 6A/20ms 200Ω: 2A/20ms 2000Ω: 15mA/360ms	20 / 200 / 2000Ω Auto-Ranging	±(3%rdg+4dgt)
L-PE (ATT)	100 ~ 260V 50/60Hz	L-N: 6A/30ms N-PE: 10mA approx. 4s	20 / 200 / 2000Ω Auto-Ranging L-N < 20 Ω	±(3%rdg+6dgt)
I-N/I-L	100 ~ 500V 50/60Hz	20Ω: 6A/20ms	20Ω	±(3%rdg+4dgt)

PSC (L-N/L-L) / PFC (L-PE)

PSC	100~500V 50/60Hz	6A/20ms	2000A/20kA Auto-Ranging	PSC accuracy is derived from measured loop impedance specification and measured voltage specification
PFC	100~260V 50/60Hz	6A/20ms 2A/20ms 15mA/360ms	2000A/20kA Auto-Ranging	
PFC (ATT)	100~260V 50/60Hz	L-N: 6A/30ms N-PE: 10mA/approx. 4s	2000A/20kA Auto-Ranging	

RCD

Function	Rated Voltage	Accuracy				
		Trip Current		Trip Time		
		AC Type	A Type			
X1/2	230V+ 10%-15% 50/60Hz	-8%~2%	±10%	±(1%rdg+3dgt)		
X1		+ 2% ~ + 8%				
X5		+ 2% ~ + 8%				
Ramp (▲)		± 4%				
Auto	Depending on the accuracy at each function Measurement sequence: X1/2 0°>X1 180°>X1 0°>X1 180°> X5 0°> X5 180° Measurements with X5 aren't carried out when current is 300mA or more.					
Continuity / Insulation / Loop / PSC ranges uses the rolling average						