

1.6X0.8mm SMD CHIP LED LAMP

Part Number: KPT-1608LVVBC-D Blue



ATTENTION OBSERVE PRECAUTIONS FOR HANDLING **ELECTROSTATIC** DISCHARGE SENSITIVE **DEVICES**


Features


- 1.6mmX0.8mm SMD LED, 0.75mm thickness.
- Low power consumption.
- Wide viewing angle.
- Ideal for backlight and indicator.
- Package: 2000pcs / reel .
- Moisture sensitivity level : level 3.
- Low current IF=2mA operating.
- RoHS compliant.


Descriptions

- The Blue source color devices are made with InGaN Light Emitting Diode.
- Electrostatic discharge and power surge could damage the LEDs.
- It is recommended to use a wrist band or antielectrostatic glove when handling the LEDs.
- All devices, equipments and machineries must be electrically grounded.

Package Dimensions







- 1. All dimensions are in millimeters (inches).
- 2. Tolerance is $\pm 0.1 (0.004")$ unless otherwise noted.
- The specifications, characteristics and technical data described in the datasheet are subject to change without prior notice.
 The device has a single mounting surface. The device must be mounted according to the specifications.

SPEC NO: DSAO6846 **REV NO: V.1B** DATE: JAN/27/2016 PAGE: 1 OF 5 APPROVED: Wynec **CHECKED: Allen Liu** DRAWN: M.Liu ERP: 1203014458



Selection Guide

Part No.	Emitting Color (Material)	Lens Type	Iv (mcd) [2] @ 2mA		Viewing Angle [1]
		2.	Min.	Тур.	201/2
KPT-1608LVVBC-D	Blue (InGaN)	Water Clear	15	24	120°

Notes:

- 1. θ1/2 is the angle from optical centerline where the luminous intensity is 1/2 of the optical peak value.
 Luminous intensity / luminous Flux: +/-15%.
 Luminous intensity value is traceable to CIE127-2007 standards.

Electrical / Optical Characteristics at TA=25°C

Symbol	Parameter	Emitting Color	Тур.	Max.	Units	Test Conditions
λpeak	Peak Wavelength	Blue	465		nm	IF=2mA
λD [1]	Dominant Wavelength	Blue	470		nm	IF=2mA
Δλ1/2	Spectral Line Half-width	Blue	22		nm	IF=2mA
С	Capacitance	Blue	100		pF	VF=0V;f=1MHz
VF [2]	Forward Voltage	Blue	2.65	3	V	IF=2mA
lr	Reverse Current	Blue		50	uA	VR=5V

- Notes:
 1. Wavelength: +/-1nm.
 2. Forward Voltage: +/-0.1V.
 3. Wavelength value is traceable to CIE127-2007 standards.
- Excess driving current and / or operating temperature higher than recommended conditions may result in severe light degradation or premature failure.


Absolute Maximum Ratings at TA=25°C

Parameter	Values	Units
Power dissipation	90	mW
DC Forward Current	30	mA
Peak Forward Current [1]	100	mA
Electrostatic Discharge Threshold (HBM)	250	V
Reverse Voltage	5	V
Operating Temperature	re -40°C To +85°C	
Storage Temperature -40°C To +85°C		

- Notes: 1. 1/10 Duty Cycle, 0.1ms Pulse Width.
- Relative humidity levels maintained between 40% and 60% in production area are recommended to avoid the build-up of static electricity Ref JEDEC/JESD625-A and JEDEC/J-STD-033.

SPEC NO: DSAO6846 **REV NO: V.1B DATE: JAN/27/2016** PAGE: 2 OF 5 APPROVED: Wynec **CHECKED: Allen Liu** DRAWN: M.Liu ERP: 1203014458

Kingbright



 SPEC NO: DSAO6846
 REV NO: V.1B
 DATE: JAN/27/2016
 PAGE: 3 OF 5


 APPROVED: Wynec
 CHECKED: Allen Liu
 DRAWN: M.Liu
 ERP: 1203014458

Kingbright

KPT-1608LVVBC-D

Reflow soldering is recommended and the soldering profile is shown below. Other soldering methods are not recommended as they might cause damage to the product.

Reflow Soldering Profile For Lead-free SMT Process.




- NOTES:

 1.We recommend the reflow temperature 245°C(+/-5°C). The maximum soldering temperature should be limited to 260°C.


 2.Don't cause stress to the epoxy resin while it is exposed to high temperature.

 3.Number of reflow process shall be 2 times or less.


Recommended Soldering Pattern (Units: mm; Tolerance: ± 0.1)



Reel Dimension



Tape Dimensions (Units : mm)



SPEC NO: DSAO6846 APPROVED: Wynec

REV NO: V.1B CHECKED: Allen Liu


DATE: JAN/27/2016 DRAWN: M.Liu


PAGE: 4 OF 5 ERP: 1203014458

Kingbright

PACKING & LABEL SPECIFICATIONS

KPT-1608LVVBC-D







Terms and conditions for the usage of this document

- 1. The information included in this document reflects representative usage scenarios and is intended for technical reference only.
- 2. The part number, type, and specifications mentioned in this document are subject to future change and improvement without notice. Before production usage customer should refer to the latest datasheet for the updated specifications.
- 3. When using the products referenced in this document, please make sure the product is being operated within the environmental and electrical limits specified in the datasheet. If customer usage exceeds the specified limits, Kingbright will not be responsible for any subsequent issues.
- 4. The information in this document applies to typical usage in consumer electronics applications. If customer's application has special reliability requirements or have life-threatening liabilities, such as automotive or medical usage, please consult with Kingbright representative for further assistance.
- 5. The contents and information of this document may not be reproduced or re-transmitted without permission by Kingbright.
- 6. All design applications should refer to Kingbright application notes available at http://www.kingbright.com/application_notes

 SPEC NO: DSAO6846
 REV NO: V.1B
 DATE: JAN/27/2016
 PAGE: 5 OF 5

 APPROVED: Wynec
 CHECKED: Allen Liu
 DRAWN: M.Liu
 ERP: 1203014458