


SMD Power Inductors (NS series)

NS12555T680MN



■ Features

- Item Summary
68uH \pm 20%, 1.81A, 12.5x12.5x5.5mm
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 2000pcs(500pcs*4reel)

■ Products characteristics table

Inductance	68 uH \pm 20 %
Case Size (mm)	12.5x12.5
Rated Current (max)	1.81 A
Saturation Current (max)	1.81 A
Temperature Rise Current (max)	2.14 A
DC Resistance (typ)	79.7 m Ω
DC Resistance (max)	95.6 m Ω
LQ Measuring Frequency	100 kHz
Self Resonant Frequency (min)	7.9 MHz
Operating Temp. Range	-40 to +125 $^{\circ}$ C (Including-self-generated heat)
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow


■ External Dimensions

Dimension L	12.5 \pm 0.3 mm
Dimension W	12.5 \pm 0.3 mm
Dimension H	5.5 \pm 0.35 mm

■ Recommended Land Patterns

【推奨ランドパターン】
実装上の注意
・実装状態を確認の上ご使用くださいますようお願いいたします。
・本製品のはんだ付けはリフローはんだ工法に限りします。

【Recommended Land Patterns】
Surface Mounting
・Mounting and soldering conditions should be checked beforehand.
・Applicable soldering process to these products is reflow soldering only.




2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
Before making final selection, please check product specification.




SMD Power Inductors (NS series)

NS12555T680MN



Dimension	unit : mm	unit : inch
Length :	12.5 + / - 0.3	(0.492 + / - 0.012)
Width :	12.5 + / - 0.3	(0.492 + / - 0.012)
Height :	5.5 + / - 0.35	(0.217 + / - 0.014)

Inductance :	68	μ H	(test freq at 0.1MHz)
DC Resistance :	0.0797	/	0.09564 ohm (typ / max)
Saturation Current :	1.81	A (max)	
Temp. rise Current :	2.14	A (max)	
Saturation current typical : 30% reduction from initial L value.			
Temp rise Current typical : Temperature will rise by 40 deg C			



The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the data at any time without notice.
 Before making final selection, please check product specification.