

**Double-deck terminal block; Through/through terminal block; L/N;
without marker carrier; gray housing; suitable for Ex e II
applications**

Item No.: 2002-2203



Double-deck terminal block; Through/through terminal block; L/N; without marker carrier; gray housing; suitable for Ex e II applications

Marking

RoHS ✓
Compliant

Business data

Supplier	WAGO
Item no.	2002-2203
GTIN / EAN	4044918691079
Content	1
Order amount	50
Customer item number	

Notes



Technical data


Miscellaneous

Total number of connection points	4
Total number of potentials	2
Potentialkennzeichnung	L/N
Number of levels	2
Color	gray
Ratings according to 1	IEC/EN 60947-7-1
Pollution degree (1)	3
Rated voltage EN (1) [V]	500 [V]

Technical data	
Rated surge voltage (1) [kV]	6 [kV]
Nominal current [A]	24 [A]
Nominal current (2) [A]	28 [A]
Rated voltage EN (Ex e II) [V]	440 [V]
Nominal current (Ex e II) [A]	20 [A]
Nominal current (Ex e II) with jumper [A]	18 [A]
Connection technology (1)	Push-in CAGE CLAMP®
Nominal cross section 1	2.5 mm²
Solid sizes 1	0.25 ... 4 mm² / 22 ... 12 AWG
solid, directly pluggable 1	0.75 ... 4 mm² / 18 ... 12 AWG
Fine-stranded wires 1	0.25 ... 4 mm² / 22 ... 12 AWG
min. fine-stranded with insulated ferrule, push-in terminati	0.75 mm² / 18 AWG
Strip length 1	10 ... 12 mm / 0.39 ... 0.47 in
Type of wiring	Front-entry wiring
Design	horizontal
Marking level	Center/Side marking
Insulating material	Polyamide 66 (PA 66)
Fire load [MJ]	0.204 [MJ]
Weight [g]	10.153 [g]
Width	5.2 mm / 0.205 in
Height from upper-edge of DIN-rail [mm]	51.7 [mm]
Height from upper-edge of DIN-rail	51.7 mm / 2.035 in
Length	69.7 mm / 2.744 in
Type of mounting	DIN 35 rail

Images & drawings





Address

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.