

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000207](#)
Status: **Active**
Overview: [Mini-Fit Jr.™ Power Connectors](#)
Description: [Mini-Fit® Female Crimp Terminal, Tin \(Sn\) over Nickel \(Ni\), 18-24 AWG, Reel](#)

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-5556-001 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0208 (Loose)
Product Name	Mini-Fit®
UPC	800754395991

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.130/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Old Part Number	5556-SP
-----------------	---------

Reference - Drawing Numbers

Product Specification	PS-5556-001
Sales Drawing	SD-5556-SP*



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant
REACH SVHC

Not Contained Per -
ED/21/2016 (20 June 2016)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5556 Series](#)

Mates With

[5558](#) Mini-Fit® Crimp Male Terminals. Mini-Fit Jr.™ Header, Dual Row, [5566](#) , [5569](#)

Use With

[5557](#) Mini-Fit Jr.™ Receptacle Housing, [30067](#) Mini-Fit® TPA, [42474](#) Mini-Fit® BMI Panel Mount, [5559](#) Mini-Fit Jr.™ Plug Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

FineAdjust™	<u>0639002900</u>
Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire	
Hand Crimp Tool for	<u>0638190900</u>
Male and Female Crimp Terminals, 16-24 AWG Wire	
Extraction Tool	<u>0011030044</u>
FineAdjust™	<u>0639002600</u>
Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire	
FineAdjust™	<u>0639015600</u>
Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	
FineAdjust™	<u>0639023900</u>
Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	
FineAdjust™	<u>0639024900</u>
Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	
T2 Terminator™	<u>0639102600</u>
for insulation OD 2.50-2.95mm - 18-24 AWG	
T2 Terminator™ for	<u>0639102900</u>
insulation OD 1.65 – 2.05mm – 18 – 24 AWG	
T2 Terminator™	<u>0639124800</u>
for insulation OD 2.50-2.95mm optimized for 18 AWG only	
T2 Terminator™	<u>0639124900</u>
for insulation OD 2.30-2.60mm - 18-24 AWG	
FineAdjust™	<u>0639024800</u>
Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	
T2 Terminator™	<u>0639115600</u>
for insulation OD 1.90-2.30mm - 18-24 AWG	
T2 Terminator™	<u>0639123900</u>
for insulation OD 1.40-1.70mm - 18-24 AWG	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION