

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000219](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr.™ Power Connectors](#)  
**Description:** [Mini-Fit® Male Crimp Terminal, Phosphor Bronze, Gold \(Au\), 18-24 AWG, Reel](#)

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">5558</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0220 (Loose)</a>
Product Name	Mini-Fit®
UPC	800754396349

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	126.914/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Old Part Number	5558PBGS
-----------------	----------

**Reference - Drawing Numbers**

Sales Drawing	SD-5558-002
---------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any  
non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[5558 Series](#)

**Mates With**

[5556 Mini-Fit® Crimp Terminal](#)

**Use With**

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FineAdjust™  
Applicator for

[0639002900](#)

Insulation OD  
 1.65-2.05mm, 18-24  
 AWG Wire  
 Hand Crimp Tool for [0638190900](#)  
 Male and Female  
 Crimp Terminals,  
 16-24 AWG Wire  
 Extraction Tool [0011030044](#)  
 FineAdjust™ [0639002600](#)  
 Applicator for  
 Insulation OD  
 2.50-2.95mm, 18-24  
 AWG Wire  
 FineAdjust™ [0639015600](#)  
 Applicator for  
 Insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 FineAdjust™ [0639023900](#)  
 Applicator for  
 Insulation OD  
 1.40-1.70mm - 18-24  
 AWG  
 FineAdjust™ [0639024900](#)  
 Applicator for  
 Insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 T2 Terminator™ [0639102600](#)  
 for insulation OD  
 2.50-2.95mm - 18-24  
 AWG  
 T2 Terminator™ for [0639102900](#)  
 insulation OD 1.65  
 – 2.05mm – 18 – 24  
 AWG  
 T2 Terminator™ [0639124800](#)  
 for insulation OD  
 2.50-2.95mm  
 optimized for 18  
 AWG only  
 T2 Terminator™ [0639124900](#)  
 for insulation OD  
 2.30-2.60mm - 18-24  
 AWG  
 FineAdjust™ [0639024800](#)  
 Applicator for  
 Insulation OD  
 2.50-2.95mm  
 Optimized for 18  
 AWG Only  
 T2 Terminator™ [0639115600](#)  
 for insulation OD  
 1.90-2.30mm - 18-24  
 AWG  
 T2 Terminator™ [0639123900](#)  
 for insulation OD  
 1.40-1.70mm - 18-24  
 AWG

This document was generated on 07/20/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**