

High Value Multilayer Ceramic Capacitors (High dielectric type)

GMK325BJ225MN-T



■ Features

- Item Summary
2.2uF±20%, 35V,
X5R/B, 1210/3225 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 2000pcs

■ Products characteristics table

Capacitance	2.2 uF ± 20 %
Case Size (EIA/JIS)	1210/3225
Rated Voltage	35 V
tan δ (max)	3.5 %
Temperature Characteristic (EIA)	X5R
Operating Temp. Range (EIA)	-55 to +85 °C
Temperature Characteristic (JIS)	B
Operating Temp. Range (JIS)	-25 to +85 °C
HALT (% Rated Voltage)	200 %
Insulation Resistance (min)	500 MΩ · μF
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 ±0.30 mm
Dimension W	2.5 ±0.20 mm
Dimension T	1.9 ±0.20 mm
Dimension e	0.60 ±0.30 mm






2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

RoHS compliance product

○GMK325BJ225MN

35V 3225 B/X5R 2.2uF +/- 20% t=2.1mmMAX
35V 1210 B/X5R 2.2uF +/- 20% t=0.083inchMAX



部品特性は設置環境、測定条件等により変化する場合があります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the data at any time without notice.

Before making final selection, please check product specification.