

## Medium-High Voltage Multilayer Ceramic Capacitors

## HMK212B7104KG-T



## ■ Features

- Item Summary  
0.1 $\mu$ F $\pm$ 10%, 100V,  
X7R, 0805/2012 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 3000pcs

## ■ Products characteristics table

Capacitance	0.1 $\mu$ F $\pm$ 10 %
Case Size (EIA/JIS)	0805/2012
Rated Voltage	100 V
$\tan \delta$ (max)	3.5 %
Temperature Characteristic (EIA)	X7R
Operating Temp. Range (EIA)	-55 to +125 °C
HALT (% Rated Voltage)	200 %
Insulation Resistance (min)	100 M $\Omega$ · $\mu$ F
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

## ■ External Dimensions

Dimension L	2.0 $\pm$ 0.10 mm
Dimension W	1.25 $\pm$ 0.10 mm
Dimension T	1.25 $\pm$ 0.10 mm
Dimension e	0.50 $\pm$ 0.25 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.

# Multi Layer Ceramic Capacitor

# TAIYO YUDEN






-Electrical Characteristics Data-

14QA11

RoHS compliance product

## ○HMK212B7104KG

100V 2012 X7R 0.1uF +/- 10% t=1.35mmMAX  
100V 0805 X7R 0.1uF +/- 10% t=0.053inchMAX



部品特性は設置環境、測定条件等により変化する場合があります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the data at any time without notice.

Before making final selection, please check product specification.