


Standard Multilayer Ceramic Capacitors (Temperature compensating type)

UMK105CG100DV-F



■ Features

- Item Summary
10pF $\pm$ 0.5pF, 50V,
C0G/CG, 0402/1005 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping paper 10000pcs

■ Products characteristics table

Capacitance	10 pF $\pm$ 0.5pF
Case Size (EIA/JIS)	0402/1005
Rated Voltage	50 V
Q (min)	600 at 1MHz
Temperature Characteristic (EIA)	C0G
Operating Temp. Range (EIA)	-55 to +125 °C
Temperature Characteristic (JIS)	CG
Operating Temp. Range (JIS)	-55 to +125 °C
Temperature Characteristic	0 $\pm$ 30 ppm/°C
HALT (% Rated Voltage)	200 %
Insulation Resistance (min)	10 G Ω
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	1.0 $\pm$ 0.05 mm
Dimension W	0.5 $\pm$ 0.05 mm
Dimension T	0.5 $\pm$ 0.05 mm
Dimension e	0.25 $\pm$ 0.10 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

Multi Layer Ceramic Capacitor

TAIYO YUDEN

-Electrical Characteristics Data-






13CDD05

RoHS compliance product

○UMK105CG100DV

50V 1005 CG/C0G 10pF +/- 0.5pF t=0.55mmMAX

50V 0402 CG/C0G 10pF +/- 0.5pF t=0.022inchMAX



部品特性は設置環境、測定条件等により変化することがあります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the Date at any time without notice.

Before making final selection, please check product specification