



Datasheet for part number CA08COMP14S-5S

| |
|--|
| Our Catalog Part Number: CA08COM-PG14S-5S |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA COM |

| Product Datasheet | |
|--|---|
| Thread | Connector with Threaded Coupling |
| Shell Style | Plug, 90° |
| Endbell Style | Endbell for PG cable gland termination |
| Gender | Socket |
| Shell Size | 14S |
| Contact Arrangement | 14S-5 |
| Number of contacts | 5 contacts size 16S |
| Contact Type | Solder Cup |
| Contact Plating | Hard silver |
| Contacts installed | yes |
| Contact Rating at +20 °C (68 °F) (Size 15/15S/16/16S) | 22 A |
| Contact Resistance (Size 15/15S/16/16S) | 6 mΩ |
| Operating Voltage | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41. |
| Insulator Resistance | ≥1000 MΩ |
| Test Voltage | 1050 Vrms |
| Air and Creepage Paths (Min) | 0,7 mm |
| Ambient Temperature | Standard insulator material -55°/+125°C (-67/257°F) |
| Safety Provisions | IP67 (only applies if a grommet is used) |
| Mating Cycles | 500 min |
| Sep. Force per Contact (Size 15/15S/16/16S) | 1,0 N |
| Gage | For infos on Gage please see catalog VG95234, part 1 |
| Coupling Torque | Closing: 3,0 Nm max / Opening: 0,35 Nm min |
| Contact Retention (Size 15/15S/16/16S) | 35 N |
| Shell Material | Aluminium alloy |
| Shell Plating | Nickel plated |
| Insulator and Gromet Material | CR-Elastomere |
| Contact Material | Copper alloy |
| Harnessing Info: Contact Cross-Section | See assembly instruction |
| Harnessing Info: Insulator Diameter | See assembly instruction |
| Wire Stripping (Size 15/15S/16/16S) | 6,2 mm |
| General Info | <i>All tests in accordance with VG95319 and/or if applicable with VG95210 except salt spray resistance and heat and humidity endurance test</i> |