



# Agilent 363xA-Series Programmable dc Power Supplies

Data Sheet



- Single and triple outputs
- 80W to 200W output power
- Dual output ranges (except E3631A)
- Low noise and excellent regulation
- High accuracy and resolution
- Remote sense (except E3631A)
- Front and rear output terminals (E3633/34A only)
- GPIB and RS-232 standard

## Clean and stable power with programmability at an affordable price

### Affordable programmable power supplies to meet your needs

The E363xA-series of programmable dc power supplies give you the performance of system power supplies without the high price. All models give you clean power, dependable regulation and fast transient response with built-in GPIB and RS-232 interface. E363xA-series are designed to meet the most demanding applications in R&D design verifications, production testing, and QA verifications with traditional quality and reliability you can count on.

### Excellent Performance you can trust

0.01% load and line regulation keep the output steady when power line and load change occur. The power supplies specify both normal mode

voltage/current noise and common mode current noise. The low normal mode noise specification assures clean power for precision circuitry applications and the low common mode current provides isolation from power line current injection.

### Remote Interface

If you have an IEEE-488 card or RS-232 in a PC, these power supplies will work for you. Every model comes equipped with both GPIB and RS-232 as standard. All programming is done in easy to use SCPI (Standard Commands for Programmable Instruments). The user's guide describes the process for first time programmers.

### Front Panel Operation

A knob and self-guiding keypads allow you to set the output at the resolution you need for the most exacting adjustments quickly and easily. Up to three complete power supply setups can be stored and

recalled from the internal non-volatile memory. The output on/off button sets the output to zero.

### E3631A triple-output power supply

This famous 80-watt triple output supply offers three independent 0 to +6 V/5 A and 0 to  $\pm 25$  V/1 A outputs. The 6V output is electrically isolated from the  $\pm 25$  V supply to minimize any interference between circuits under tests. The  $\pm 25$  V outputs can be set to track each other.

### E3632A/33A/34A single-output dual range power supplies

These single output power supplies give you the flexibility to select from dual output ranges. Output load is protected against overvoltage and overcurrent, which are easily monitored and adjusted from the front panel and remote interface. Remote sense is available to eliminate the errors due to voltage drops on the load leads. E3633A/34A offers front and rear output terminals.



Agilent Technologies

### E3631A/32A/33A/34A Programmable dc Power Supply Specifications

Model Number	E3631A			E3632A	E3633A	E3634A
	1	2	3			
<b>dc Output</b> Rating (0°C to 40°C)	0 to +6 V, 0 to 5 A	0 to +25 V, 0 to 1 A	0 to -25 V, 0 to 1 A	0 to 15 V / 7 A or 0 to 30 V / 4 A	0 to 8 V / 20 A or 0 to 20 V / 10 A	0 to 25 V / 7 A or 0 to 50 V / 4 A
<b>Load Regulation</b> <sup>1</sup> ±(% of output + offset)	<0.01% + 2 mV <0.01% + 250 uA					
<b>Line Regulation</b> ±(% of output + offset)	<0.01% + 2 mV <0.01% + 250 uA					
<b>Ripple and Noise</b> (20 Hz to 20 MHz)						
Normal Mode Voltage	<350 uVrms / 2 mVpp				<350 uVrms / 3 mVpp	<500 uVrms / 3 mVpp
Normal Mode Current	<2 mArms	<500 uArms		<2 mArms		
Common Mode Current	<1.5 uArms					
<b>Accuracy 12 Mos</b> (25°C + 5°C), ± (% output + offset)						
Programming						
Voltage	0.1% + 5 mV	0.05% + 20 mV		0.05% + 10 mV		
Current	0.2% + 10 mA	0.15% + 4 mA		0.2% + 10 mA		
Readback						
Voltage	0.1% + 5 mV	0.05% + 10 mV		0.05% + 5 mV		
Current	0.2% + 10 mA	0.15% + 4 mA		0.15% + 5 mA		
<b>Resolution</b>						
Program	0.5 mV / 0.5 mA	1.5 mV / 0.1 mA		1 mV / 0.5 mA	1 mV / 1 mA	3 mV / 0.5 mA
Readback	0.5 mV / 0.5mA	1.5 mV / 0.1mA		0.5 mV / 0.1mA	0.5 mV / 1mA	1.5 mV / 0.5 mA
Meter	1 mV / 1mA	10 mV / 1mA		1 mV / 1mA	1 mV / 1 mA (<10 A), 10 mA (≥10 A)	
<b>Transient Response</b>	Less than 50 usec for output to recover to within 15 mV following a change in output current from full load to half load or vice versa.					
<b>Command Processing Time</b> <sup>2</sup>	<100 msec					
<b>OVP/OCP</b>						
Accuracy, ±(% output + offset)	N/A			0.5% + 0.5 V / 0.5% + 0.5 A		
Activation time	N/A			1.5 msec, OVP ≥3 V / <10 msec, OVP <3 V and OCP		
<b>Temperature Coefficient per °C</b> ± (% output + offset)						
Voltage	0.01% + 2 mV	0.01% + 3 mV				
Current	0.02% + 3 mA	0.02% + 0.5 mA		0.02% + 3 mA		
<b>Stability</b> , constant output & temperature ± (% of output + offset), 8 hrs						
Voltage	0.03% + 1 mV	0.02% + 2 mV		0.02% + 1 mV		
Current	0.1% + 3 mA	0.05% + 1 mA		0.1% + 1 mA		
<b>Remote Sense</b> Max voltage in each load lead				1 V	0.7 V	
<b>Voltage Programming Speed</b> , to within 1% of total excursion						
Up	Full Load	11 msec	50 msec		50 msec	95 msec
	No Load	10 msec	45 msec		20 msec	45 msec
Down	Full Load	13 msec	20 msec		45 msec	30 msec
	No Load	200 msec	400 msec		400 msec	450 msec
<b>AC Input</b> (47 Hz - 63 Hz)	100 Vac ±10% (Opt 0E9) / 115 Vac ±10% (Std) / 230 Vac ±10% (Opt 0E3)					
<b>Dimension/Net Weight</b>	213 mm W x 133 mm H x 348 mm D (8.4 x 5.2 x 13.7 in) / 8.2 kg (18 lbs)			213 mm W x 133 mm H x 348 mm D (8.4 x 5.2 x 13.7 in) / 9.5 kg (21 lbs)		
<b>Warranty</b>	1 year					
<b>Product Regulation</b>	Certified to CSA 22.2 No. 231 (for E3631A), No. 1010.1 (for E3632A/33A/34A); conforms to IEC 1010-1; carries CE mark; complies with CISPR-11, Group 1, Class A					

Note: 1. With sense terminal connected for E3632A/33A/34A.

2. Maximum time for output to change after receipt of commands.

### Ordering Information

E3630-Series Power Supplies  
E3631A 80-Watt  
Triple Power Supply  
E3632A 120-Watt  
Single Power Supply  
E3633A/34A 200-Watt  
Single Power Supply

### Power Options

Opt. 0E3 230 Vac  $\pm$  10%  
Opt. 0EM 115 Vac  $\pm$  10%  
Opt. 0E9 100 Vac  $\pm$  10%

### Other Options

Opt. 0L2 Extra manual sets  
Opt. 1CM Rack-mount kit\*

### Rack Mount Kits\*

E3631A/32A/33A/34A  
To rack mount two instruments side by side  
Lock-link Kit  
(P/N 5061-9694)  
Flange Kit  
(P/N 5063-9214)  
To rack mount two instruments in a sliding  
support shelf  
Support Shelf (P/N 5063-9256)  
Slide Kit (P/N 1494-0015) required for  
support shelf

\*Rackmounting with 1CM or lock-link/flange kit  
requires Agilent or customer supplied support rails  
Agilent Support Rails - E3663AC

### Agilent Technologies' Test and Measurement Support, Services, and Assistance

Agilent Technologies aims to maximize the value you receive, while minimizing your risk and problems. We strive to ensure that you get the test and measurement capabilities you paid for and obtain the support you need. Our extensive support resources and services can help you choose the right Agilent products for your applications and apply them successfully. Every instrument and system we sell has a global warranty. Support is available for at least five years beyond the production life of the product. Two concepts underlie Agilent's overall support policy: "Our Promise" and "Your Advantage."

#### Our Promise

Our Promise means your Agilent test and measurement equipment will meet its advertised performance and functionality. When you are choosing new equipment, we will help you with product information, including realistic performance specifications and practical recommendations from experienced test engineers. When you use Agilent equipment, we can verify that it works properly, help with product operation, and provide basic measurement assistance for the use of specified capabilities, at no extra cost upon request. Many self-help tools are available.

#### Your Advantage

Your Advantage means that Agilent offers a wide range of additional expert test and measurement services, which you can purchase according to your unique technical and business needs. Solve problems efficiently and gain a competitive edge by contracting with us for calibration, extra-cost upgrades, out-of-warranty repairs, and on-site education and training, as well as design, system integration, project management, and other professional engineering services. Experienced Agilent engineers and technicians worldwide can help you maximize your productivity, optimize the return on investment of your Agilent instruments and systems, and obtain dependable measurement accuracy for the life of those products.



### Agilent Email Updates

[www.agilent.com/find/emailupdates](http://www.agilent.com/find/emailupdates)

Get the latest information on the products and applications you select.

### Agilent T&M Software and Connectivity

Agilent's Test and Measurement software and connectivity products, solutions and developer network allows you to take time out of connecting your instruments to your computer with tools based on PC standards, so you can focus on your tasks, not on your connections. Visit [www.agilent.com/find/connectivity](http://www.agilent.com/find/connectivity) for more information.

By internet, phone, or fax, get assistance with all your test & measurement needs

Online assistance:  
[www.agilent.com/find/assist](http://www.agilent.com/find/assist)

### Phone or Fax

United States:  
(tel) 1 800 829 4444

Canada:  
(tel) 1 877 894 4414  
(fax) (905) 282 6495

China:  
(tel) 800 810 0189  
(fax) 800 820 2816

Europe:  
(tel) (31 20) 547 2323  
(fax) (31 20) 547 2390

Japan:  
(tel) (81) 426 56 7832  
(fax) (81) 426 56 7840

Korea:  
(tel) (82 2) 2004 5004  
(fax) (82 2) 2004 5115

Latin America:  
(tel) (305) 269 7500  
(fax) (305) 269 7599

Taiwan:  
(tel) 0800 047 866  
(fax) 0800 286 331

Other Asia Pacific Countries:  
(tel) (65) 6375 8100  
(fax) (65) 6836 0252  
Email: [tm\\_asia@agilent.com](mailto:tm_asia@agilent.com)

Product specifications and descriptions in this document subject to change without notice.

© Agilent Technologies, Inc. 2002  
Printed in USA May 1, 2004  
5968-9726EN

