


## Wire-wound Chip Inductors for Signal Lines (LB series M type)

## LBM2016T560J



## ■ Features

- Item Summary  
56 $\mu$ H $\pm$ 5%, 95mA, 0806/2016 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping Embossed 2000pcs

## ■ Products characteristics table

Inductance	56 $\mu$ H $\pm$ 5 %
Case Size (EIA/JIS)	0806/2016
Rated Current (max)	95 mA
DC Resistance (typ)	5.9 $\Omega$
DC Resistance (max)	7.67 $\Omega$
Q (min)	20
LQ Measuring Frequency	2.52 MHz
Self Resonant Frequency (min)	12 MHz
Operating Temp. Range	-40 to +105 $^{\circ}$ C (Including-self-generated heat)
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

## ■ External Dimensions

Dimension L	2.0 $\pm$ 0.2 mm
Dimension W	1.6 $\pm$ 0.2 mm
Dimension T	1.6 $\pm$ 0.2 mm
Dimension e	0.5 $\pm$ 0.2 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.