

Multilayer Chip Inductors for High Frequency Applications (HK series)

HK16083N3S-T



■ Features

- Item Summary  
3.3nH±0.3nH, 0.3A, 0603/1608 (EIA/JIS)
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping paper 4000pcs

■ Products characteristics table

Inductance	3.3 nH ± 0.3nH
Case Size (EIA/JIS)	0603/1608
Rated Current (max)	0.3 A
DC Resistance (typ)	60 mΩ
DC Resistance (max)	120 mΩ
Q (min)	10
Q (typ)	14
LQ Measuring Frequency	100 MHz
Self Resonant Frequency (min)	6000 MHz
Self Resonant Frequency (typ)	9000 MHz
Operating Temp. Range	-40 to +85 °C
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow/Wave

■ External Dimensions

Dimension L	1.6 ±0.15 mm
Dimension W	0.8 ±0.15 mm
Dimension T	0.8 ±0.15 mm
Dimension e	0.3 ±0.2 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition. TAIYO YUDEN reserves the right to make change to the Date at any time without notice. Before making final selection, please check product specification.