

High Value Multilayer Ceramic Capacitors (High dielectric type)

JMK325BJ107MY-T



■ Features

- Item Summary
100uF±20%, 6.3V,
X5R, 1210/3225 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping Embossed 2000pcs

■ Products characteristics table

Capacitance	100 uF ± 20 %
Case Size (EIA/JIS)	1210/3225
Rated Voltage	6.3 V
tan δ (max)	10 %
Temperature Characteristic (EIA)	X5R
Operating Temp. Range (EIA)	-55 to +85 °C
HALT (% Rated Voltage)	150 %
Insulation Resistance (min)	100 MΩ · μF
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	3.2 ±0.30 mm
Dimension W	2.5 ±0.20 mm
Dimension T	1.9 +0.10/-0.20 mm
Dimension e	0.60 ±0.30 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

Multi Layer Ceramic Capacitor

TAIYO YUDEN







-Electrical Characteristics Data- 10YB08-A

RoHS compliance product

○JMK325BJ107MY

6.3V 3225 X5R 100uF +/-20% t=2.0mmMAX

6.3V 1210 X5R 100uF +/-20% t=0.079inchMAX



部品特性は設置環境、測定条件等により変化する場合があります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the Date at any time without notice.

Before making final selection, please check product specification