


Technical Data Sheet

Product: 9502NH Version: 7

Date: 8-7-2013 Page: 1 / 2

9502NH

Instrumentation and computer cable AWG24 (7xAWG32) 2 twisted pair Overall Beldfoil® + Drain wire FRNC (UV stabilised) sheath.



Applications

• For EIA RS-232 data transmission applications.

General Standards

EN 50290-2-27

Construction & Dimensions

1. Inner Conductor

Material Tinned Copper
Diameter AWG24 (7xAWG32)

2. Insulation

 $\begin{array}{ll} \text{Material} & \text{PE} \\ \text{Diameter over insulation} & 1.12 \pm 0.05 \text{ mm} \\ \text{Colour of insulation} & \text{Pair 1: Black and red} \end{array}$

Pair 2: Black and White

3. Foil (Beldfoil®)

Material Aluminium / Polyester Thickness 9 / 12 μm

4. Drain wire

Material Tinned Copper
Diameter AWG24 (7xAWG32)

5. Sheath

Material FRNC (UV stabilised)
Colour Chrome (RAL 7037)
Nominal thickness 0.90 mm

Nominal thickness 0.90 mm Nominal diameter 5.80 mm



Technical Data Sheet

Product: 9502NH Version:

8-7-2013 Date: Page: 2/2

Mechanical characteristics

Parameter	Specification	Unit
Flame resistance	IEC 60332-3-24	
Smoke density	IEC 61034	
Oil resistance	IEC 60811-404	
Radiation resistance	IEC 60544	
Application specification	EN 50290-2-27	
Halogen content according to IEC 60754-1	zero	
Corrosivity of fire gasses to IEC 60754-2		
Conductivity	≤ 100	μS/cm
pH value	≥ 4.3	
Temperature range installing	-15 to +80	°C
Temperature range operating (moving installation)	-15 to +80	°C
Temperature range operating (fixed installation)	-45 to +80	°C
Temperature range storage	-45 to +80	°C
Minimum bending radius	10 x cable diameter	
Maximum pulling tension	100	N

Electrical characteristics

Parameter	Specification	Unit
Nominal resistance conductor	78.7	Ω/km
Nominal resistance shield	55.8	Ω/km
Nominal capacitance conductor to conductor of a pair	98.4	pF/m
Nominal capacitance conductor to shield + other conductor	164.0	pF/m
Test voltage conductor-conductor	2500	VDC,3 seconds
Test voltage conductor-screen	2500	VDC,3 seconds
Voltage rating	300	V RMS
Maximum continues current per conductor @ 25 °C	1.76	Α

Belden declares this product to be in compliance with the environmental regulations EU RoHS (Directive 2011/65/EU, 02 Jan. 2013); this is valid for all material produced after the RoHS compliant date for this product.