




Home > Products > Power-duty Rocker Switches > TP > Product Page

1TP37-7



Actual product appearance may vary.

TP Series Rocker Switch, 1 pole, 3 position, Screw terminal, Above Panel Mounting

Order Product and Get Support

- U.S. Authorized Distributors
- Global Sales & Service
- N. American Sales Reps
- Distributor Inventory
- Technical Assistance
- White Papers
- Literature Request
- Test and Measurement Catalog
- RoHS Product List
- Customer Feedback

Features

Environmentally sealed
 Two and three-position pushbutton action
 Various button colors
 1, 2, and 4-pole circuitry
 Flush panel and above panel mountings
 Temperature range: -54 ° C to +71 ° C [-65 ° F to +160 ° F]
 UL recognized, CSA certified
 CE approved

Potential Applications

Industrial machinery and equipment
 Military and commercial aviation
 Marine applications
 Construction equipment
 Test instruments
 Agricultural machinery
 Process control
 Medical instrumentation

Description

MICRO SWITCH™ TP Rocker switches may be mounted flush with panel for a low-button profile or above panel for a distinct button appearance. Buttons measure 22,1 mm x 37,1 mm [.87 in x 1.46 in]. They are removable and interchangeable, and come in transparent plastic, translucent plastic, and six colors of opaque plastic. Switches without buttons are also available, as well as separate buttons.

Supporting Documentation

- ▣ [Accessory: Rocker Operator](#)
- ▣ [Engineering Drawing](#)

Product Specifications				
Circuitry/Operating action	<table border="0" style="width: 100%;"> <tr> <td style="text-align: center; vertical-align: top;"> Keyway Momentary Position </td> <td style="text-align: center; vertical-align: top;"> Center Position </td> <td style="text-align: center; vertical-align: top;"> Opposite Keyway Momentary Position </td> </tr> </table>	Keyway Momentary Position 	Center Position 	Opposite Keyway Momentary Position
Keyway Momentary Position 	Center Position 	Opposite Keyway Momentary Position 		
Product Type	MICRO SWITCH™ Rocker			
Ampere/Voltage Range (Resistive Load)	0.5 A to 10 A at 0.5 Vac to 277 Vac, 0.5 A to 18 A at 0.5 Vdc to 28 Vdc, 0.5 A at 250 Vdc, 0.75 A at 115 Vdc			
Circuitry	SPDT			
Action	3 position			
Mounting	Above Panel			
Termination	Screw			
Button Type	No button			
UL/CSA Rating Code	L192: 10 A - 125, 250, 277 Vac; 1/4 Hp - 125 Vac; 1/2 Hp - 250, 277 Vac; 3 A - 125 Vac "L"			
Comment	No mounting lugs			
Availability	Global			
UNSPSC Code	302119			
UNSPSC Commodity	302119 Switches and controls and relays			
Series Name	TP			

My Links

- [Login to iCOM](#)
- [Login as Rep/AD](#)
- [Login as Guest](#)
- [Login to Digital University](#)

Keyword Search

Search for product and support information.

All Sensing and Control

Product Search

Part number search:

Use (*) to expand search

Specification Search