



Ultrastar® 7K6000

Highlights

- Best-in-class random & sequential performance
- Reliable, field-proven, 7th generation 5-disk design
- Compared to prior generation 7K4000
 - 50% more capacity¹ (6TB vs. 4TB)
 - 30% better power efficiency (Watts/TB)
 - Up to 3X faster random write performance using media cache technology
 - 25% faster sequential read/write performance
- 12Gb/s SAS & 6Gb/s SATA
 - 12Gb/s SAS compatible with next gen data centers; backwards compatible with 6Gb/s SAS
- 128MB cache buffer improves response time and data management
- Instant Secure Erase (ISE) & Self-Encrypting Drive (SED) options
- Advanced format 4Kn and 512e models up to 6TB; 512n format available in 4TB and 2TB capacities
- 2M hours MTBF² rating & 5yr limited warranty

Applications/Environments

- Cloud & Hyperscale storage
- Distributed Files Systems like Ceph™ and Hadoop® to support Big Data Analytics
- Video surveillance & content distribution
- Direct & Network Attached Storage (DAS & NAS)
- RAID arrays
- Massive scale-out data centers (MSO)



6TB, 5TB, 4TB and 2TB | 7200 RPM
SATA 6Gb/s and SAS 12Gb/s



Increasing Capacity Density by 50%

As petabyte (PB) growth continues to increase at a rapid pace, corporate and cloud data centers are under extreme pressure to improve the efficiency of storage. To address this data center challenge, HGST introduces Ultrastar® 7K6000, delivering up to 6TB of capacity in an industry-standard, 3.5-inch hard drive, for capacity-optimized enterprise applications. Ultrastar 7K6000 provides 50% more capacity and 30% better power efficiency in terms of Watts per terabyte (W/TB) than its predecessor, Ultrastar 7K4000. The 7K6000 is designed for all traditional and rapidly growing scale-out storage applications, including object, block and file storage architectures, providing huge capacity, the fastest 7,200 RPM performance and the best \$/TB acquisition cost.



Technology Innovation Improves Storage Efficiency

Ultrastar 7K6000 also delivers greater storage efficiency through best-in-class performance, achieving up to 3X higher random write performance, thanks to HGST media cache architecture, a disk-based caching technology, which provides a large non-volatile cache on the disk. Media cache also allows for improved reliability and data integrity during unexpected power loss. Other performance-enhancing features include higher areal density for 25% faster sequential performance vs. 7K4000, and a 128MB cache buffer. The 7K6000 offers a 12Gb/s SAS (6Gb/s SATA) interface for easy integration into high performance data centers. As drive capacities increase, so does the time required to recover a failed drive in a RAID configuration. Dramatically reduce RAID rebuild times and maintain system performance during the rebuild process with the new Rebuild Assist. Learn more in our Rebuild Assist technical brief. For legacy systems that require native 512 formatting, models are available at 4TB and 2TB capacity points.



Data Security with Industry-Leading Quality, Reliability

Compliance and privacy requirements drive the need for increased data security. Ultrastar 7K6000 helps protect data from unauthorized use by offering security and encryption options. Instant Secure Erase (ISE) models expedite drive redeployment and retirement. Encryption models protect data with hardware-based encryption, including a Trusted Computing Group (TCG) Enterprise_A, TCG with FIPS 140-2 certification, Level 2. The Ultrastar 7K6000 is a seventh generation, 5-platter design, field proven by top server and storage OEMs, and Internet giants, and extends HGST's long-standing tradition of reliability leadership with a 2M-hour MTBF rating and a 5-year limited warranty.

Features & Benefits

| Feature / Function | Benefits | |
|--------------------|--|--|
| Capacity | <ul style="list-style-type: none"> • 6TB, 5TB, 4TB, and 2TB • Advanced Format up to 6TB • 512n Format available on 4TB and 2TB | <ul style="list-style-type: none"> • Represents 50% more capacity than prior generation for lower TCO in the data center • Enables higher capacities • Compatibility with legacy systems |
| Power Efficiency | 30% lower Watts per terabyte (W/TB) | Improved power efficiency compared to prior generation |
| Performance | <ul style="list-style-type: none"> • Increased Areal Density (Gbits/sq. in) • Media cache architecture • Rebuild Assist mode • SAS 12Gb/s and SATA 6Gb/s • Rotational Vibration Safeguard (RVS) | <ul style="list-style-type: none"> • Enables 25% higher sequential performance (6TB) vs. prior generation Ultrastar 7K4000 • Up to 3X better random write performance vs. prior generation • Reduces rebuild time for a failed drive and maintains system performance during rebuild in a RAID configuration • Provides compatibility and easy integration with high-performance data centers • Maintains drive performance in high rotational vibration environments and multi-drive systems |
| Reliability | <ul style="list-style-type: none"> • 2.0M hours MTBF and 0.44% AFR • 5-year limited warranty | <ul style="list-style-type: none"> • Industry's highest reliability rating for Capacity Enterprise hard drives • Industry's best for enterprise-class hard drives |
| Data Security | <ul style="list-style-type: none"> • Instant Secure Erase • Optional Bulk Data Encryption (SATA) & TCG Enterprise_A (SAS) | <ul style="list-style-type: none"> • Enables swift and efficient drive redeployment and retirement • Hardware-based encryption protects data from unauthorized use |



Ultrastar® 7K6000

Specifications

| | SATA Models | SAS Models |
|---|---|--|
| Model / Part No. | HUS7260xxALN61y HUS7260xxALE61y HUS7260xxALA61y | HUS7260xxAL421y HUS7260xxAL521y HUS7260xxALS21y |
| Configuration | | |
| Interface | SATA 6Gb/s | SAS 12Gb/s |
| Capacity (TB) ¹ | 6TB / 5TB / 4TB / 2TB | ← |
| Sector size (bytes) ³ | 4Kn: 4096, 512n*/512e: 512 | 4Kn: 4096, 4112, 4160, 4224 512n*/512e: 512, 520, 528 |
| Max. areal density (Gbits/sq. in.) | 512e/4Kn: 703 (6TB), 599 (<6TB) 512n*: 623 | ← |
| Performance | | |
| Data buffer (MB) ⁴ | 128 | ← |
| Rotational speed (RPM) | 7200 | ← |
| Latency average, (ms) | 4.16 | ← |
| Interface transfer rate (MB/s, max) | 600 | 1200 |
| Sustained transfer rate ⁵ (MiB/sec, typ.) | 216 (6TB), 192 (<6TB) | ← |
| (MB/sec, typ.) | 227 (6TB), 202 (<6TB) | ← |
| Seek time (read/write, ms, typical) ⁶ | 7.6 / 8.0 | ← |
| Reliability | | |
| Error rate (non-recoverable, bits read) | 1 in 10 ¹⁵ | ← |
| Load/Unload cycles (at 40°C) | 600,000 | ← |
| MTBF ² (M hours) | 2.0 | ← |
| Annualized Failure Rate ² (AFR) | 0.44% | ← |
| Availability (hrs/day x days/wk) | 24x7 | ← |
| Warranty (yrs) | 5 | ← |
| Acoustics | | |
| Idle/Operating (Bels, typical) | 2.9 / 3.6 | ← |
| Power | | |
| Requirement | +5V, +12V | ← |
| Operating (W, typical) ⁷ | 9.1 | 11.0 |
| Idle (W) ⁸ | 7.1 | 7.7 |
| Power consumption efficiency at idle (Watts/TB) | 1.2 (6TB) | 1.3 (6TB) |
| (Watts/GB) | 0.0012 (6TB) | 0.0013 (6TB) |
| Physical size | | |
| z-height (mm, max) | 26.1 | ← |
| Dimensions (width x depth, mm) | 101.6 (+/-0.25) x 147 | ← |
| Weight (g, max) | 715 | ← |

NOTE: See "How to read the Ultrastar model number" for possible values for xx and y

| | SATA Models | SAS Models |
|----------------------------------|-------------|------------|
| Environmental (operating) | | |
| Ambient temperature | 5° to 60° C | ← |
| Shock (half-sine wave 2 ms, G) | 70 | ← |
| Vibration (G RMS, 5 to 500 Hz) | 0.67 (XYZ) | ← |

| | SATA Models | SAS Models |
|--------------------------------------|---------------|------------|
| Environmental (non-operating) | | |
| Ambient temperature | -40° to 70° C | ← |
| Shock (half-sine wave, 1ms, G) | 300 | ← |
| Vibration (G RMS, 5 to 500 Hz) | 1.04 (XYZ) | ← |

- ¹ One MB is equal to one million bytes, one GB is equal to one billion bytes and one TB equals 1,000GB (one trillion bytes) when referring to hard drive capacity. Accessible capacity will vary from the stated capacity due to formatting and partitioning of the hard drive, the computer's operating system, and other factors.
- ² MTBF and AFR targets are based on a sample population and are estimated by statistical measurements and acceleration algorithms under median operating conditions. MTBF and AFR ratings do not predict an individual drive's reliability and do not constitute a warranty.
- ³ Advanced Format drive: 4K (4096-byte) physical sector
- ⁴ Portion of buffer capacity used for drive firmware
- ⁵ MiB/s is 2²⁰ bytes, MB/s is 10⁶ bytes
- ⁶ Excludes command overhead
- ⁷ SATA models: 8K Queue Depth = 1, SAS models: 4K Queue Depth = 4
- ⁸ Idle specification is based on use of Idle_A

How to read the Ultrastar model number

Example: HUS7260xxAL421y = xTB, 4Kn SAS 12Gb/s

| | |
|--------------------------------------|--|
| H = HGST | 42 = Interface, 4Kn SAS 12Gb/s |
| U = Ultrastar | 52 = 512e SAS 12Gb/s |
| S = Standard (vs. C for Compact) | E6 = 512e SATA 6Gb/s |
| 72 = 7200 RPM | N6 = 4Kn SATA 6Gb/s |
| 60 = Full capacity — 6TB | A6* = 512n SATA 6Gb/s |
| xx = Capacity this model | S2* = 512n SAS 12Gb/s |
| 60 = 6TB, 50 = 5TB, | 1 = 128MB buffer |
| 40 = 4TB, 20 = 2TB | y = Data Security Mode |
| A = Generation code | 0 = Instant Secure Erase |
| L = 26.1mm z-height | 1 = Bulk Data Encryption (SATA), TCG SED encryption (SAS) |
| *Available in 4TB and 2TB capacities | 4 = Secure Erase (overwrite only) |
| | 5 = TCG encryption with FIPS (SAS) |

HGST Quality and Service

HGST's Ultrastar 7K6000 extends the company's long-standing tradition of performance and capacity leadership. The proven drive design enables high reliability and availability to customer data. Ultrastar quality, performance and world class technical support and service provides customers with a lower total cost of ownership over previous generations.

HGST drives are backed by an array of technical support and services, which may include customer and integration assistance. HGST is dedicated to providing a complete portfolio of HDD/SSD solutions to satisfy today's monumental computing needs.

© 2014-2015 HGST, Inc. 3403 Yerba Buena Road, San Jose, CA 95135 USA. Produced in the United States 9/14, rev. 12/14, 8/15, 9/15, 12/15. All rights reserved. Ultrastar is a registered trademark of HGST, Inc. and its affiliates in the United States and/or other countries. Other trademarks are property of their respective companies. HGST trademarks are intended and authorized for use only in countries and jurisdictions in which HGST has obtained the rights to use, market and advertise the brand. Contact HGST for additional information. HGST shall not be liable to third parties for unauthorized use of this document or unauthorized use of its trademarks.

References in this publication to HGST's products, programs, or services do not imply that HGST intends to make these available in all countries in which it operates.

Product specifications provided are sample specifications and do not constitute a warranty. Information is true as of the date of publication and is subject to change. Actual specifications for unique part numbers may vary.

Please visit the Support section of our website, www.hgst.com/support, for additional information on product specifications. Photographs may show design models.

Information & Technical Support

www.hgst.com
www.hgst.com/support

Partners First Program

channelpartners@hgst.com
www.hgst.com/partners