


LW Reversal Decoupling Capacitors (LWDC™)

JWK105C7224MP-F



■ Features

- Item Summary
0.22 μ F $\pm$ 20%, 6.3V,
X7S, 0204/0510 (EIA/JIS)
- Lifecycle Stage
Mass Production
- Standard packaging quantity (minimum)
Taping paper 10000pcs

■ Products characteristics table

Capacitance	0.22 μ F $\pm$ 20 %
Case Size (EIA/JIS)	0204/0510
Rated Voltage	6.3 V
$\tan \delta$ (max)	10 %
Temperature Characteristic (EIA)	X7S
Operating Temp. Range (EIA)	-55 to +125 °C
HALT (% Rated Voltage)	150 %
Insulation Resistance (min)	500 M Ω · μ F
RoHS2 Compliance	Yes
REACH Compliance	Yes
Soldering	Reflow

■ External Dimensions

Dimension L	0.52 $\pm$ 0.05 mm
Dimension W	1.0 $\pm$ 0.05 mm
Dimension T	0.3 $\pm$ 0.05 mm
Dimension e	0.18 $\pm$ 0.08 mm

2016.01.25

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.
 Before making final selection, please check product specification.

Multi Layer Ceramic Capacitor

TAIYO YUDEN

-Electrical Characteristics Data-





13YC05

RoHS compliance product

○JWK105C7224MP

6.3V 0510 X7S 0.22uF +/- 20% t=0.35mmMAX

6.3V 0204 X7S 0.22uF +/- 20% t=0.014inchMAX



部品特性は設置環境、測定条件等により変化することがあります。本データをご使用される際は実際の製品特性に対する参考データとしてご利用ください。また、本データは予告無く追加・削除及び変更を行う場合があります。ご注文の際は、納入仕様書のご確認をお願いします。

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.

TAIYO YUDEN reserves the right to make change to the Date at any time without notice.

Before making final selection, please check product specification