DC/AC MicroProbe Model K100



The Model K100 has exceptional AC/ DC current measurement capabilities. Very small and compact, this microprobe is designed for accurate measurement of very low currents with 50µADc sensitivity.

Its very small size and "clip" shape make it ideal for probing and measuring in tight wiring areas such as circuit boards, 4 to 20mA process loops or automotive electronic circuitry. Model K100 is an excellent companion to all DMMs and instruments that will benefit from the probe's high sensitivity, dynamic range and waveform displaying characteristics.

The Model K100 provides a 1 mV/mA output and is designed for versatility and general low current applications. It provides AC + DC output signal proportional to the total current under test, without the need of probe ranging or signal filtering. True RMS measurements with total AC + DC components are possible.

Features

- Measures extremely low level DC from 100µA
- Outputs signal proportional to total current (AC + DC)
- Low noise
- Ultra-compact size and non-contact clamp-on convenience
- Simple plug-in operation
- Designed for use with DMMs and oscilloscopes
- · Accurate display of wave forms
- No range or mode (AD/DC) switching required
- · Extended battery life
- Red LED indicates momentary or continuous overload
- Green LED indicates power and battery condition
- Double Insulation
- CE Mark

ECHNICAL Assistance (800) 343-1391

Applications

- Industrial process controls (4 to 20mA current loops)
- Electronic circuit design, testing and repair
- Automobile wiring and engine control systems
- Avionics systems maintenance and repair
- · Shipboard maintenance and repair
- Fault and signal location in complex networks
- Ground and leakage current measurement
- Pre-deployment testing of power-conscious equipment


Specifications

MODELS	K100	
ELECTRICAL		
Nominal Range	0 to 3Arms/0 to 4.5Abc	
Measurement Range	0 to ±4.5A	
Output Signal	< 100µV, DC to 3kHz	
Accuracy (4.5A Range)		
AC	±2.0% of Reading ± 200µA	
DC	±1% of Reading ± 200µA	
Overload	Red LED indicates momentary or continuous overload	
Frequency Range	DC to 2kHz (@ -3dB sine)	
Load Impedance	200Ω	
Working/Common Mode Voltage	300V, EN 61010-1, Cat. II	
Battery	9V Alkaline, NEDA 1604, 6LR61 or IEC 6 LF22	
Output Termination	(Approx. 20 hours life) 4mm Safety Banana Plugs	
MECHANICAL	4mm Salety Danana Flugs	
Operating Temperature	-14° to 131°F (-10° to 55°C)	
Storage Temperature	-40° to 176°F (-40° to 80°C)	
Operating Relative Humidity	<95% @ ≤ 35°C, 75% @ 55°C	
Zero Adjustment	±25mA approx. by 10 turn knob at base of case	
Maximum Conductor Size	3/16", 0.180" (4.5mm)	
Dimensions	Probe: 4.4 x 0.6 x 1.0" (111 x 15 x 25mm); Electronic Module: 4.9 x 2.5 x 1.1" (124 x 64 x 28mm)	
Weight	9 oz (250g)	
SAFETY		
Electrical	EN 61010-2-32	
Double Insulation 回	Yes	
CE Mark	Yes	

Note: Reference conditions: 23°C ±3°C, 20 to 75%RH, battery voltage 9V ±0.1V; earth's magnetic field <40A/m; absence of AC fields; input impedance of display device ≥ 1MΩ/100pF; DC or sinusoidal AC current 45 to 65Hz.



DC/AC MicroProbe Model K100 (pdf) 02/08 Rev. 03



(19mm) spacing

ORDERING INFORMATION	CATALOG NO.
AC/DC Microprobe Model K100 (Lead – 1mV/mA – 4.5A max) Includes a 9V battery and user manual	Cat. #1200.67



DC/AC MicroProbe Model K100 (pdf) 02/08 Rev. 03

Contact Us

United States and Canada:

Chauvin Arnoux[®], Inc. d.b.a. AEMC[®] Instruments 200 Foxborough Blvd. Foxborough, MA 02035 USA (508) 698-2115 • Fax (508) 698-2118 www.aemc.com

Customer Support – for placing an order, obtaining price and delivery: customerservice@aemc.com

Sales Department – for general sales information: sales@aemc.com

Repair and Calibration Service – for information on repair and calibration, obtaining a user manual: repair@aemc.com

Technical and Product Application Support – for technical and application support: techinfo@aemc.com

Webmaster – for information regarding www.aemc.com: webmaster@aemc.com

South America, Central America, Mexico, Caribbean, Australia and New Zealand:

Chauvin Arnoux[®], Inc. d.b.a. AEMC[®] Instruments 15 Faraday Drive Dover, NH 03820 USA (978) 526-7667 • Fax (978) 526-7605 export@aemc.com www.aemc.com

All other countries:

Chauvin Arnoux SCA 190, rue Championnet 75876 Paris Cedex 18, France 33 1 44 85 45 28 • Fax 33 1 46 27 73 89 info@chauvin-arnoux.com www.chauvin-arnoux.com



DC/AC MicroProbe Model K100 (pdf) 02/08 Rev. 03