


**KEMET Part Number: C0603T104K5RALTU**  
(C0603T104K5RAL7867)

Capacitor, Ceramic, SMD, MLCC, COTS, Temperature Stable, Class II, 0.1 uF, +/-10% Tol, 50 V, X7R, 0603 (1608 metric)



General Information	
Supplier:	KEMET
Application:	COTS Military Equivalent: A Testing
Chip Size:	0603 (1608 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, COTS, Temperature Stable, Class II
Termination Type:	Tin-Lead (SnPb)
Marked:	No
RoHS:	No

Dimensions (mm)		
Symbol	Dimension	Tolerance
T	0.8	+/-0.07
L	1.6	+/-0.15
W	0.8	+/-0.15
B	0.35	+/-0.15
S	0.7	MIN

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Paper Tape
Package Quantity:	4000

Specifications	
Capacitance:	0.1 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Dissipation Factor:	2.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	5 GOhm
Dielectric Strength:	125 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours