

NEW




Accessory


- 1 or 2 channel types
 - Daily and weekly program
 - 46 memory locations
 - Minimum interval 1 min
 - Switching capacity 16 A per channel
 - Permanent by date-mode (holiday function)
 - Permanently ON or OFF with manual switch (Perm ON/OFF)
 - Manual override
 - Automatic sorting of switching times on readout
 - Unrestricted block programming of days
 - Fully automatic daylight saving time (European, North American or Australian standard adjustable)
 - Elapsed time and pulse counter for each channel
 - Pulse function: Automated switch OFF timer up to 59:59 (mm:ss)
 - Security by PIN-Coding
 - Illuminated display
- Accessory: Data-key Save 'n carry**
(Not included in delivery of the time switch)
- Data-key for managing the programming data:
 - Data back-up of the time switch
 - Programming the time switch with the key program
 - Time switch executes only the key program
 - Query of the key program
 - Data-key Save 'n carry
Order-No.: 22262 DK pro
 - PC Programming Package Save 'n carry PP 50 pro
Start of serial production: March 2008

Highlights


- Text based Menu and self-explanatory symbols
- Display with a large dot matrix area to provide two high resolution text lines
- Easy handling. Quick and intuitive programmable time switch
- Can be programmed with supply disconnected (6 years battery-reserve)
- Unlimited program security by E²-PROM
- Data-key Save 'n carry – programmable with PC Programming package Save 'n carry PP 50 pro (optional – not included in delivery content)



SC 28.11 pro (1 channel)



SC 28.21 pro (2 channels)



Programmable time switch SC 28.X1 pro
for DIN-rail mounting

Technical data	
Supply Voltage	230 V, 50–60 Hz
Power consumption	approx. 1.5 VA
Channel (potential-free)	Change-over, contact gap < 3 mm (µ)
Contact material	AgCdO
Switching capacity	16 A / 250 V~ at cosφ=1
Filament Lamp	1,000 W
Halogen Lamp	1,000 W
Fluorescent Lamp uncompensated	500 VA
Fluorescent Lamp series compensated	500 VA
Fluorescent Lamp parallel compensated	300 VA
Fluorescent Lamp double switch.	500 VA
Mercury Discharge Lamp uncompensated	2 x 125 W, 1 x 250 W
Mercury Discharge Lamp parallel compensated	3 x 50 W (7 µF), 2 x 125 W (10 µF), 1 x 250 W (18 µF)
Sodium Discharge Lamp uncompensated	1 x 150 W
Sodium Discharge Lamp parallel compensated	—
Compact Fluorescent Lamp convent. lamp ballast	500 VA
Compact Fluorescent Lamp electron. lamp ballast	2 x electronic lamp ballast, power independent
Switching functions	ON, OFF, pulse
Pulse length	00:01 mm:ss up to 59:59 mm:ss
Memory locations	46
Minimum interval	1 min
Time base	Quartz crystal
Power back-up (at 20°C)	approx. 6 years (depends on the Lithium-battery life)
Program security	unlimited (E ² -PROM)
Quartz cryst. accuracy (at 20°C)	≤ ±1 sec/day
Display	high resolution LCD (visible area 7.5 cm ²)
Permitted ambient temperature	–10°...+55°C
Enclosure	self-extinguishing thermoplastic
Dimensions	45 x 35 x 58 mm
Distribution board mounting	35 mm DIN-rail (DIN EN 50022)
Type of connection	Screw terminals (pull-up type)
Type of protection	IP 20 to DIN EN 60529
Class of protection	II when installed according to regulations

Rights to technical amendments reserved.

Type/Order No.	Channels	Time Base	Special function
SC 28.11 pro	1	Quartz	data-key (optional)
SC 28.21 pro	2	Quartz	data-key (optional)