

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0510040900](#)
Status: **Active**
Overview: MicroBlade™ Connection System
Description: 2.00mm Pitch MicroBlade™ Wire-to-Board Housing, Friction Lock, 5.80mm Height, 9 Circuits

Documents:

[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Drawing \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General

Product Family Crimp Housings
 Series 51004
 Application Signal, Wire-to-Board
 MolexKits Yes
 Overview MicroBlade™ Connection System
 Product Name MicroBlade™
 UPC 800753754706

Physical

Circuits (maximum) 9
 Flammability 94V-0
 Gender Receptacle
 Glow-Wire Compliant No
 Lock to Mating Part Yes
 Material - Resin Polyester
 Net Weight 242.700/mg
 Number of Rows 1
 Packaging Type Bag
 Panel Mount No
 Pitch - Mating Interface 2.00mm
 Stackable No
 Temperature Range - Operating -20°C to +85°C


Electrical

Current - Maximum per Contact 2.0A

Material Info

Reference - Drawing Numbers

Product Specification RPS-51004-002, RPS-51004-003, RPS-51004-008,
 RPS-51004-010, RPS-51004-012, RPS-51004-013,
 RPS-51004-018, RPS-51004-019, RPS-51004-024
 Sales Drawing SD-51004-**00



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/21/2016 (20 June
 2016)

Halogen-Free

Status

Not Low-Halogen

**Need more information on product
 environmental compliance?**

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any
 non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

51004 Series

Mates With

53014 , 53015 , 53025 MicroBlade™
 Headers

Use With

50011 Crimp Terminal