

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0430310003](#)  
**Status:** **Active**  
**Overview:** Micro-Fit 3.0™ Connectors  
**Description:** Micro-Fit 3.0™ Crimp Terminal, Male, with 0.76µm Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-43045 \(PDF\)](#) [Product Literature \(PDF\)](#)

**General**

Product Family	Crimp Terminals
Series	<a href="#">43031</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<u>Micro-Fit 3.0™ Connectors</u>
Packaging Alternative	<a href="#">43031-0009 (Loose)</a>
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0™
UPC	800754369435

**Physical**

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm²	N/A


**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-43045
Sales Drawing	SD-43031-****



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**China RoHS**

**REACH SVHC**

Not Contained Per -  
ED/21/2016 (20 June  
2016)

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[43031](#) Series

**Mates With**

[43030](#) Micro-Fit 3.0™ Female Crimp Terminals

**Use With**

[43020](#) , [43640](#) Micro-Fit 3.0™ Plug Housings, [44300](#) Micro-Fit BMI™ Panel Mount Plug Housings

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

FineAdjust™ Applicator for Insulation OD 1.10-1.30mm - 20-24 AWG	<u>0639018800</u>
FineAdjust™ Applicator for Insulation OD 0.91-1.09mm - 20-24 AWG	<u>0639018900</u>
FineAdjust™ Applicator for Insulation OD 1.30-1.85mm, 20-24 AWG Wire	<u>0639004500</u>
T2 Terminator™ for insulation OD 0.91-1.09mm - 20-24 AWG	<u>0639118900</u>
T2 Terminator™ for insulation OD 1.30-1.85mm - 20-24 AWG	<u>0639104500</u>
T2 Terminator™ for insulation OD 1.10-1.30mm - 20-24 AWG	<u>0639118800</u>
Hand Crimp Tool	<u>0638190000</u>
Extraction Tool	<u>0011030043</u>
Insertion Tool for Crimp Terminal	<u>0638120800</u>

This document was generated on 07/29/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**