

Capacitor, ceramic, 2.2 pF, +/-0.5pF Tol, 200 V, C0G, Lead Spacing=0.1"



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	3.81	MAX
H	3.14	MAX
T	2.54	MAX
S	2.54	NOM
LL	7	MIN
F	0.51	NOM

**Packaging Specifications**

Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	500

**General Information**

Supplier:	KEMET
Application:	General Purpose
Temperature Coefficient:	C0G
Body Type:	Radial Conformal
Lead Type:	Wire Leads
Termination Type:	Tin (Sn)
RoHS:	Yes

**Specifications**

Capacitance:	2.2 pF
Voltage:	200 V
Tolerance:	+/-0.5pF
Temperature Range:	-55/+125C
Failure Rate:	N/A
Dissipation Factor:	0.1%
Insulation Resistance:	100 GOhm
Dielectric Strength:	500 V