

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0836119006](#)
Status: **Active**
Overview: Commercial Micro-D High-Density Connectors
Description: 1.27mm Pitch Commercial Micro D, PCB Mount, Right Angle Plug, 9 Circuits

Documents:

[3D Model](#) [Packaging Specification PK-83098-636 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	83611
Application	Wire-to-Board
Comments	Pin Contact
Component Type	Plug
Overview	Commercial Micro-D High-Density Connectors
Product Name	Commercial Micro-D
Type	N/A
UPC	800754026239

Physical

Circuits (Loaded)	9
Circuits (maximum)	9
Durability (mating cycles max)	500
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Net Weight	4.479/g
Orientation	Right Angle
PC Tail Length	2.79mm
PCB Retention	Yes
PCB Thickness - Recommended	1.52mm
Packaging Type	Tube
Panel Mount	Yes
Pitch - Mating Interface	1.27mm
Plating min - Mating	0.381µm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40°C to +125°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	1.0A
Shielded	Yes
Voltage - Maximum	350V AC

Solder Process Data

Duration at Max. Process Temperature (seconds)	030
Lead-free Process Capability	WAVE

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-83098-636
Sales Drawing	SD-83611-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[83611 Series](#)

Mates With

[83421](#) , [83424](#) , [83423](#)

This document was generated on 07/18/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION