





## Index

<b>Product</b>	<b>Page</b>
<b>SNAPConnect® Toggle and Decorator Series</b>	
SNAPConnect® Toggle Series . . . . .	D-4
SNAPConnect® Decorator Series . . . . .	D-5
<b>HBL® Extra Heavy Duty Industrial Grade</b>	
Toggle and Locking Type Switches with Ground Screw . . . . .	D-6
Toggle Type Illuminated and Pilot Light Switches with Ground Screw . . . . .	D-7
3-Position, 2-Circuit Center Off Switches . . . . .	D-7
<b>Hubbell-PRO Heavy Duty Industrial Series</b>	
Toggle Switches . . . . .	D-8
Pre-Wired/Leaded Switches . . . . .	D-8
Hospital Call Switch with Lanyard . . . . .	D-8
<b>Pre-Wired/Leaded Commercial Toggle and Decorator Switches . . . . .</b>	
<b>Specification Grade Commercial Switches . . . . .</b>	
<b>Style Line® Decorator Series Specification Grade . . . . .</b>	
<b>Extra Heavy Duty Industrial 347V AC Toggle and PresSwitch® . . . . .</b>	
<b>Switch Accessories</b>	
Pilot Light, SWITCHOUT® Lockout Device and Weatherproof Switch Plates for Toggle Switches . . . . .	D-13
<b>Switch Certification Chart . . . . .</b>	
<b>Nylon and Metal Wallplates . . . . .</b>	
<b>Dimmers</b>	
Slide and Rotary Control Dimmers . . . . .	D-16
Dimmer Ganging and Derating . . . . .	D-17
<b>Heavy Duty Panel Mount and Bat Handle Switches . . . . .</b>	
<b>Technical Information . . . . .</b>	


SNAPConnect® Switches




Toggle Switches




Pre-Wired/Leaded Switches



PresSwitch® and  
Panel Mount Switches





**Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**



3 Wire Connector for Single Pole and Single Pole Illuminated

**SNAPSP1NA  
SNAPSP2NA**




4 Wire Connector for Single Pole Pilot Light Switch

**SNAPSP1NA  
SNAPSP2NA**



4 Wire Connector for Three Way and Three Way Illuminated

**SNAP3W1NA  
SNAP3W2NA**



Steel, nickel plated bridge is corrosion resistant

Prominent amperage marking allows easy identification of rating

Abuse resistant nylon toggle

One piece rivetless copper alloy spring contact arm and terminal plate assures proper contact alignment providing long life

One piece bridge with integral grounding terminal with #8 brass screw provides a low resistance ground path

Stainless steel automatic grounding clip assures grounding continuity between mounting strap and metal wall box

Thread cleaning captive mounting screw

Strip gauge for accurate wiring

Large silver alloy contacts reduce contact erosion providing long life

Back wire entrance points for terminations accept two wires for feed through capability avoiding pigtailing

Large brass binding head screws with deep slots secure wire connections

Color coded base identifies amperage when terminating connections, 15A (Blue), 20A (Red), and 30A (Green)

**HBL1221I**



One piece rivetless copper alloy spring contact arm and terminal plate assures proper contact alignment reducing heat rise. Large silver alloy contacts reduce contact erosion and prevent welding, providing long life.



Elastomer rocker assures quiet operation and precise timing. Permanently lubricated assembly provides long life and trouble free operation.




Heavy duty nylon toggle resists abuse and chemical attack making it suitable for use in the toughest environments.




One piece integral grounding terminal with #8 brass screw allows compliance to NEC®. Stainless steel automatic self-grounding clip assures grounding continuity between mounting strap and metal wall box. Steel nickel plated mounting strap provides a corrosion resistant finish.

NEC® is a registered trademark of the National Fire Protection Association (NFPA).






SNAP1201INA



SNAP1221BKNA



SNAPSWJUMP



SNAP3W1NA

## HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP

Dimensions in Inches (mm)

SNAPConnect® Specification Grade Toggle Series, Assembled in USA  
15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
SNAPConnect® Toggle.	Black	SNAP1201BKNA	—	SNAP1203BKNA	—
	Brown	SNAP1201BRNA	—	SNAP1203BRNA	—
	Gray	SNAP1201GYNA	—	SNAP1203GYNA	—
	Ivory	SNAP1201INA	—	SNAP1203INA	—
	Lt. Almond	SNAP1201LANA	—	SNAP1203LANA	—
	Red	SNAP1201RNA	—	SNAP1203RNA	—
	White	SNAP1201WNA	—	SNAP1203WNA	—

## 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
SNAPConnect® Toggle.	Black	SNAP1221BKNA	—	SNAP1223BKNA	—
	Brown	SNAP1221BRNA	—	SNAP1223BRNA	—
	Gray	SNAP1221GYNA	—	SNAP1223GYNA	—
	Ivory	SNAP1221INA	—	SNAP1223INA	—
	Lt. Almond	SNAP1221LANA	—	SNAP1223LANA	—
	Red	SNAP1221RNA	—	SNAP1223RNA	—
	White	SNAP1221WNA	—	SNAP1223WNA	—

Illuminated, Light On with Load Off  
15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Illuminated, Light On with Load Off, Toggle, Blue LED.	Black	SNAP1201ILBKNA	—	SNAP1203ILBKNA	—
	Ivory	SNAP1201ILINA	—	SNAP1203ILINA	—
	Red	SNAP1201ILRNA	—	SNAP1203ILRNA	—
	White	SNAP1201ILWNA	—	SNAP1203ILWNA	—

## 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Illuminated, Light On with Load Off, Toggle, Blue LED.	Black	SNAP1221ILBKNA	—	SNAP1223ILBKNA	—
	Ivory	SNAP1221ILINA	—	SNAP1223ILINA	—
	Red	SNAP1221ILRNA	—	SNAP1223ILRNA	—
	White	SNAP1221ILWNA	—	SNAP1223ILWNA	—

Pilot, Light On with Load On  
15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Pilot, Light On with Load On, Toggle, Red LED.	Black	SNAP1201PLBKNA	—	—	—
	Ivory	SNAP1201PLINA	—	—	—
	Red	SNAP1201PLRNA	—	—	—
	White	SNAP1201PLWNA	—	—	—

## 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Pilot, Light On with Load On, Toggle, Red LED.	Black	SNAP1221PLBKNA	—	—	—
	Ivory	SNAP1221PLINA	—	—	—
	Red	SNAP1221PLRNA	—	—	—
	White	SNAP1221PLWNA	—	—	—

## Jumper/Tester

Description	Catalog Number
Jumper/Tester for Single Pole Circuits, Black Toggle, Blue LED Indicator.	SNAPSWJUMP
Jumper/Tester for Three Way Circuits, Black Toggle, Blue LED Indicator.	SNAP3WJUMP

## SNAPConnect® Switch Pigtailed Connector, Assembled in USA

Description	3 Wire Connector for Single Pole and Single Pole Illuminated	4 Wire Connector for Single Pole and Three Way with Pilot Light	4 Wire Connector for 3 Way and 3 Way Illuminated
Clear right angle terminal, 6 inch leads, solid wire.	SNAPSP1NA	SNAPSP1NA	SNAP3W1NA
Clear right angle terminal, 6 inch leads, stranded wire.	SNAPSP2NA	SNAPSP2NA	SNAP3W2NA

Note: See page D-13 for accessories.

See page D-15 for wallplates.

See page D-20 for technical information.

Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.

# Switches

## 15 and 20 Ampere, 120-277 Volts AC

SNAPConnect® Heavy Duty Style Line® Decorator Switches



### SNAPConnect® Spec. Grade Style Line® Decorator Series, Assembled in USA 15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
SNAPConnect® Rocker.	Black	<b>SNAP2101BKNA</b>	—	<b>SNAP2103BKNA</b>	—
	Brown	<b>SNAP2101BRNA</b>	—	<b>SNAP2103BRNA</b>	—
	Gray	<b>SNAP2101GYNA</b>	—	<b>SNAP2103GYNA</b>	—
	Ivory	<b>SNAP2101INA</b>	—	<b>SNAP2103INA</b>	—
	Lt. Almond	<b>SNAP2101LANA</b>	—	<b>SNAP2103LANA</b>	—
	Red	<b>SNAP2101RNA</b>	—	<b>SNAP2103RNA</b>	—
	White	<b>SNAP2101WNA</b>	—	<b>SNAP2103WNA</b>	—

### 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
SNAPConnect® Rocker.	Black	<b>SNAP2121BKNA</b>	—	<b>SNAP2123BKNA</b>	—
	Brown	<b>SNAP2121BRNA</b>	—	<b>SNAP2123BRNA</b>	—
	Gray	<b>SNAP2121GYNA</b>	—	<b>SNAP2123GYNA</b>	—
	Ivory	<b>SNAP2121INA</b>	—	<b>SNAP2123INA</b>	—
	Lt. Almond	<b>SNAP2121LANA</b>	—	<b>SNAP2123LANA</b>	—
	Red	<b>SNAP2121RNA</b>	—	<b>SNAP2123RNA</b>	—
	White	<b>SNAP2121WNA</b>	—	<b>SNAP2123WNA</b>	—

### Illuminated, Light On with Load Off 15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Illuminated, Light On with Load Off, Rocker, Blue LED.	Black	<b>SNAP2101ILBKNA</b>	—	<b>SNAP2103ILBKNA</b>	—
	Ivory	<b>SNAP2101ILINA</b>	—	<b>SNAP2103ILINA</b>	—
	Red	<b>SNAP2101ILRNA</b>	—	<b>SNAP2103ILRNA</b>	—
	White	<b>SNAP2101ILWNA</b>	—	<b>SNAP2103ILWNA</b>	—

### 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Illuminated, Light On with Load Off, Rocker, Blue LED.	Black	<b>SNAP2121ILBKNA</b>	—	<b>SNAP2123ILBKNA</b>	—
	Ivory	<b>SNAP2121ILINA</b>	—	<b>SNAP2123ILINA</b>	—
	Red	<b>SNAP2121ILRNA</b>	—	<b>SNAP2123ILRNA</b>	—
	White	<b>SNAP2121ILWNA</b>	—	<b>SNAP2123ILWNA</b>	—

### Pilot, Light On with Load On 15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Pilot, Light On with Load On, Rocker, Red LED.	Black	<b>SNAP2101PLBKNA</b>	—	—	—
	Ivory	<b>SNAP2101PLINA</b>	—	—	—
	Red	<b>SNAP2101PLRNA</b>	—	—	—
	White	<b>SNAP2101PLWNA</b>	—	—	—

### 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Pilot, Light On with Load On, Rocker, Red LED.	Black	<b>SNAP2121PLBKNA</b>	—	—	—
	Ivory	<b>SNAP2121PLINA</b>	—	—	—
	Red	<b>SNAP2121PLRNA</b>	—	—	—
	White	<b>SNAP2121PLWNA</b>	—	—	—

### Jumper/Tester

Description	Catalog Number
Jumper/Tester for Single Pole Circuits, Black Toggle, Blue LED Indicator.	<b>SNAPSWJUMP</b>
Jumper/Tester for Three Way Circuits, Black Toggle, Blue LED Indicator.	<b>SNAP3WJUMP</b>

### SNAPConnect® Switch Pigtailed Connector, Assembled in USA


Description	3 Wire Connector for Single Pole and Single Pole Illuminated	4 Wire Connector for Single Pole with Pilot Light	4 Wire Connector for 3 Way and 3 Way Illuminated
Clear right angle terminal, 6 inch leads, solid wire.	<b>SNAPSP1NA</b>	<b>SNAPSP1NA</b>	<b>SNAP3W1NA</b>
Clear right angle terminal, 6 inch leads, stranded wire.	<b>SNAPSP2NA</b>	<b>SNAPSP2NA</b>	<b>SNAP3W2NA</b>

Note: See page D-13 for accessories.


See page D-15 for wallplates.

See page D-20 for technical information.


**Many of these products are Assembled in USA, as indicated, and many are Buy American Compliant. Please contact Hubbell with any certification requirements.**




**SNAP2101INA**



**SNAP2121ILINA**




**SNAPSWJUMP**




### HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP


Dimensions in Inches (mm)




HBL1221




HBL3031



HBL1221L and Key



HBL1209



HBL1222RKL and Key

Dimensions in Inches (mm)

### HBL Extra Heavy Duty Industrial Series, Back and Side Wired

#### 15A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Black	<b>HBL1201BK</b>	—	<b>HBL1203BK</b>	<b>HBL1204BK</b>
	Brown	<b>HBL1201</b>	<b>HBL1202</b>	<b>HBL1203</b>	<b>HBL1204</b>
	Gray	<b>HBL1201GY</b>	—	<b>HBL1203GY</b>	<b>HBL1204GY</b>
	Ivory	<b>HBL1201I</b>	<b>HBL1202I</b>	<b>HBL1203I</b>	<b>HBL1204I</b>
	Light Almond	<b>HBL1201LA</b>	—	—	—
	Red	<b>HBL1201R</b>	—	—	—
	White	<b>HBL1201W</b>	—	<b>HBL1203W</b>	<b>HBL1204W</b>

#### 20A, 120-277V AC

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Black	<b>HBL1221BK</b>	<b>HBL1222BK</b>	<b>HBL1223BK</b>	<b>HBL1224BK</b>
	Brown	<b>HBL1221</b>	<b>HBL1222</b>	<b>HBL1223</b>	<b>HBL1224</b>
	Gray	<b>HBL1221GY</b>	<b>HBL1222GY</b>	<b>HBL1223GY</b>	<b>HBL1224GY</b>
	Ivory	<b>HBL1221I</b>	<b>HBL1222I</b>	<b>HBL1223I</b>	<b>HBL1224I</b>
	Light Almond	<b>HBL1221LA</b>	<b>HBL1222LA</b>	<b>HBL1223LA</b>	<b>HBL1224LA</b>
	Office White	<b>HBL1221OW</b>	<b>HBL1222OW</b>	<b>HBL1223OW</b>	<b>HBL1224OW</b>
	Red	<b>HBL1221R</b>	<b>HBL1222R</b>	<b>HBL1223R</b>	<b>HBL1224R</b>
	White	<b>HBL1221W</b>	<b>HBL1222W</b>	<b>HBL1223W</b>	<b>HBL1224W</b>

#### 30A, 120-277V AC

Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle.	Brown	<b>HBL3031</b>	<b>HBL3032</b>	<b>HBL3033</b>	—
	Ivory	<b>HBL3031I</b>	<b>HBL3032I</b>	<b>HBL3033I</b>	—
	White	—	<b>HBL3032W</b>	—	—

### HBL Extra Heavy Duty Industrial Locking Series, Back and Side Wired

#### 15A, 120-277V AC

Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Key Guide, back and side wired.	Black	<b>HBL1201L</b>	<b>HBL1202L</b>	<b>HBL1203L</b>	<b>HBL1204L</b>
	Gray	<b>HBL1201LG</b>	<b>HBL1202LG</b>	<b>HBL1203LG</b>	<b>HBL1204LG</b>
	Ivory	<b>HBL1201LI</b>	<b>HBL1202LI</b>	<b>HBL1203LI</b>	<b>HBL1204LI</b>
	White	<b>HBL1201LW</b>	<b>HBL1202LW</b>	<b>HBL1203LW</b>	<b>HBL1204LW</b>
Key for Locking switch.		<b>HBL1209*</b>			

#### 20A, 120-277V AC

Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Key Guide, back and side wired.	Black	<b>HBL1221L</b>	<b>HBL1222L</b>	<b>HBL1223L</b>	<b>HBL1224L</b>
	Gray	<b>HBL1221LG</b>	<b>HBL1222LG</b>	<b>HBL1223LG</b>	<b>HBL1224LG</b>
	Ivory	<b>HBL1221LI</b>	<b>HBL1222LI</b>	<b>HBL1223LI</b>	<b>HBL1224LI</b>
	White	<b>HBL1221LW</b>	<b>HBL1222LW</b>	<b>HBL1223LW</b>	<b>HBL1224LW</b>
Key for Locking switch.		<b>HBL1209*</b>			

### HBL Extra Heavy Duty Industrial AC Barrel Key Locking Switch†, Back and Side Wired

#### 20A, 120-277V AC

Description	Key Guide Color	Single Pole	Double Pole	Three Way	Four Way
Chrome operator, back and side wired.	Chrome	<b>HBL1221RKL**</b>	<b>HBL1222RKL**</b>	<b>HBL1223RKL**</b>	<b>HBL1224RKL**</b>
Replacement Barrel Key.		<b>HBL1209RKL*</b>			

Note: Keys are supplied with each locking switch. For extra keys order HBL1209.

\*Not UL Listed, CSA Certified.

\*\*Not Fed. Spec.

† See Wallplate section, page N-17 for wallplates.

See page D-13 for accessories.

See page D-15 for wallplates.

See page D-20 for technical information.

#### HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP

# Switches


## 15, 20 and 30 Ampere, 120-277 and 347 Volts AC

HBL® Extra Heavy Duty Industrial Series



### HBL Extra Heavy Duty Industrial Series, Illuminated Toggle Switches, Light On with Load Off, Back and Side Wired


Description	Toggle Color	Rating	Single Pole	Double Pole	Three Way
Nylon toggle, back and side wired.	Ivory	15A 120-277V AC	<b>HBL1201IL</b>	—	<b>HBL1203IL</b>
	Ivory	20A 120-277V AC	<b>HBL1221IL</b>	—	<b>HBL1223IL</b>
	Clear		<b>HBL1221ILC</b>	—	<b>HBL1223ILC</b>
	Red		<b>HBL1221ILR</b>	—	—



**HBL1221ILC**

### HBL Extra Heavy Duty Industrial Series, Pilot Light Switches, Light On with Load On, Back and Side Wired


Description	Toggle Color	Rating	Single Pole	Double Pole	Three Way
Nylon toggle, back and side wired.	Red	15A 120-277V AC	<b>HBL1201PL</b>	—	<b>HBL1203PL</b>
	Red	20A 120-277V AC	<b>HBL1221PL</b>	<b>HBL1222PL</b>	<b>HBL1223PL</b>
	Clear		<b>HBL1221PLC</b>	—	<b>HBL1223PLC</b>
	Green		<b>HBL1221PLG</b>	—	—
	Red	30A 120-277V AC	<b>HBL3031PL</b>	<b>HBL3032PL</b>	—



**HBL1221PL**

### Momentary Contact, Specification Grade, Three Position, Two Circuit, Center Off, Back and Side Wired


Description	Toggle Color	15A, 120-277V AC	20A, 120-277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1556</b>	<b>HBL1557</b>
	Gray	<b>HBL1556GY</b>	<b>HBL1557GY</b>
	Ivory	<b>HBL1556I</b>	<b>HBL1557I</b>
	Red	<b>HBL1556R</b>	—
	White	<b>HBL1556W</b>	<b>HBL1557W</b>
Key guide, back and side wired.	Black	<b>HBL1556L</b>	<b>HBL1557L</b>
	Gray	<b>HBL1556LG</b>	<b>HBL1557LG</b>
	Ivory	<b>HBL1556LI</b>	<b>HBL1557LI</b>
	White	<b>HBL1556LW</b>	<b>HBL1557LW</b>
Key for Locking switch.		<b>HBL1209*</b>	



**HBL1209**

### Maintained Contact, Specification Grade, Three Position, Two Circuit, Center Off, Single Pole, Double Throw


Description	Toggle Color	15A 120-277V AC	20A 120-277V AC	30A 120-277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1381</b>	<b>HBL1385</b>	—
	Ivory	<b>HBL1381I</b>	<b>HBL1385I</b>	—
	White	—	<b>HBL1385W</b>	—



**HBL1381**

### Three Position, Two Circuit, Center Off, Double Pole, Double Throw

Description	Toggle Color	15A 120-277V AC	20A 120-277V AC	30A 120-277V AC
Nylon toggle, back and side wired.	Brown	<b>HBL1382</b>	<b>HBL1386</b>	<b>HBL1388</b>
	Ivory	<b>HBL1382I</b>	<b>HBL1386I</b>	<b>HBL1388I</b>
Locking.		—	<b>HBL1386L</b>	—
Key for Locking switch.		—	<b>HBL1209*</b>	—



**HBL1386I**

Note: Keys are supplied with each locking switch. For extra keys order HBL1209.

\*Not UL Listed, CSA Certified.

See page D-13 for accessories.


See page D-15 for wallplates.

See page D-20 for technical information.

#### HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP


Dimensions in Inches (mm)



1201BK

**Hubbell-PRO Heavy Duty Industrial Series, 15A, 120-277V AC**


Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	1201AL	—	1203AL	—
	Black	1201BK	—	1203BK	—
	Brown	1201B	—	1203B	—
	Gray	1201GY	—	1203GY	—
	Ivory	1201I	—	1203I	—
	Light Almond	1201LA	—	1203LA	—
	White	1201W	—	1203W	—



1221I

**Hubbell-PRO Heavy Duty Industrial Series, 20A, 120-277V AC**


Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	1221AL	1222AL	1223AL	1224AL
	Black	1221BK	1222BK	1223BK	1224BK
	Brown	1221B	1222B	1223B	1224B
	Gray	1221GY	1222GY	1223GY	1224GY
	Ivory	1221I	1222I	1223I	1224I
	Light Almond	1221LA	1222LA	1223LA	1224LA
	Red	1221R	1222R	1223R	1224R
	White	1221W	1222W	1223W	1224W



1221PWI

**Hubbell-PRO Pre-Wired/Leaded Heavy Duty Industrial Series 20A, 120-277V AC - 8" #12 AWG THHN**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, Pre-wired leads.	Almond	1221PWAL	1222PWAL	1223PWAL	1224PWAL
	Black	1221PWBK	1222PWBK	1223PWBK	1224PWBK
	Brown	1221PWB	1222PWB	1223PWB	1224PWB
	Gray	1221PWGY	1222PWGY	1223PWGY	1224PWGY
	Ivory	1221PWI	1222PWI	1223PWI	1224PWI
	Light Almond	1221PWLA	1222PWLA	1223PWLA	1224PWLA
	Red	1221PWR	1222PWR	1223PWR	1224PWR
	White	1221PWW	1222PWW	1223PWW	1224PWW



HBL1221IHCS

**Hubbell-PRO Hospital Call Switch, with Lanyard 20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Gray	HBL1221GHCS	—	—	—
	Ivory	HBL1221IHCS	—	—	—
	White	HBL1221WHCS	—	—	—

Note: See page D-13 for accessories.  
See page D-15 for wallplates.  
See page D-20 for technical information.

Dimensions in Inches (mm)

**HP Conversion Chart**

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP






**Pre-Wired/Leaded Toggle Series Specification Grade 15A, 120-277V AC - 8" #12 AWG THHN**



Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, Nylon, Pre-wired leads.	Almond	<b>CSL115AL</b>	<b>CSL215AL</b>	<b>CSL315AL</b>	<b>CSL415AL</b>
	Black	<b>CSL115BK</b>	<b>CSL215BK</b>	<b>CSL315BK</b>	<b>CSL415BK</b>
	Brown	<b>CSL115</b>	<b>CSL215</b>	<b>CSL315</b>	<b>CSL415</b>
	Gray	<b>CSL115GY</b>	<b>CSL215GY</b>	<b>CSL315GY</b>	<b>CSL415GY</b>
	Ivory	<b>CSL115I</b>	<b>CSL215I</b>	<b>CSL315I</b>	<b>CSL415I</b>
	Light Almond	<b>CSL115LA</b>	<b>CSL215LA</b>	<b>CSL315LA</b>	<b>CSL415LA</b>
	Office White	<b>CSL115OW</b>	<b>CSL215OW</b>	<b>CSL315OW</b>	<b>CSL415OW</b>
	White	<b>CSL115W</b>	<b>CSL215W</b>	<b>CSL315W</b>	<b>CSL415W</b>

**20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, Nylon, Pre-wired leads.	Almond	<b>CSL120AL</b>	<b>CSL220AL</b>	<b>CSL320AL</b>	<b>CSL420AL</b>
	Black	<b>CSL120BK</b>	<b>CSL220BK</b>	<b>CSL320BK</b>	<b>CSL420BK</b>
	Brown	<b>CSL120</b>	<b>CSL220</b>	<b>CSL320</b>	<b>CSL420</b>
	Gray	<b>CSL120GY</b>	<b>CSL220GY</b>	<b>CSL320GY</b>	<b>CSL420GY</b>
	Ivory	<b>CSL120I</b>	<b>CSL220I</b>	<b>CSL320I</b>	<b>CSL420I</b>
	Light Almond	<b>CSL120LA</b>	<b>CSL220LA</b>	<b>CSL320LA</b>	<b>CSL420LA</b>
	Office White	<b>CSL120OW</b>	<b>CSL220OW</b>	<b>CSL320OW</b>	<b>CSL420OW</b>
	Red	<b>CSL120R</b>	<b>CSL220R</b>	<b>CSL320R</b>	<b>CSL420R</b>
	White	<b>CSL120W</b>	<b>CSL220W</b>	<b>CSL320W</b>	<b>CSL420W</b>




**Pre-Wired/Leaded Decorator Series Specification Grade 15A, 120-277V AC - 8" #12 AWG THHN**



Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, Polycarbonate, Pre-wired leads.	Almond	<b>DSL115AL</b>	—	<b>DSL315AL</b>	—
	Black	<b>DSL115BK</b>	—	<b>DSL315BK</b>	—
	Brown	<b>DSL115</b>	—	<b>DSL315</b>	—
	Gray	<b>DSL115GY</b>	—	<b>DSL315GY</b>	—
	Ivory	<b>DSL115I</b>	—	<b>DSL315I</b>	—
	Light Almond	<b>DSL115LA</b>	—	<b>DSL315LA</b>	—
	Office White	<b>DSL115OW</b>	—	<b>DSL315OW</b>	—
	White	<b>DSL115W</b>	—	<b>DSL315W</b>	—

**20A, 120-277V AC**

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, Polycarbonate, Pre-wired leads.	Almond	<b>DSL120AL</b>	<b>DSL220AL</b>	<b>DSL320AL</b>	<b>DSL420AL</b>
	Black	<b>DSL120BK</b>	<b>DSL220BK</b>	<b>DSL320BK</b>	<b>DSL420BK</b>
	Brown	<b>DSL120</b>	<b>DSL220</b>	<b>DSL320</b>	<b>DSL420</b>
	Gray	<b>DSL120GY</b>	<b>DSL220GY</b>	<b>DSL320GY</b>	<b>DSL420GY</b>
	Ivory	<b>DSL120I</b>	<b>DSL220I</b>	<b>DSL320I</b>	<b>DSL420I</b>
	Light Almond	<b>DSL120LA</b>	<b>DSL220LA</b>	<b>DSL320LA</b>	<b>DSL420LA</b>
	Office White	<b>DSL120OW</b>	<b>DSL220OW</b>	<b>DSL320OW</b>	<b>DSL420OW</b>
	White	<b>DSL120W</b>	<b>DSL220W</b>	<b>DSL320W</b>	<b>DSL420W</b>



**Illuminated, Light On with Load Off 20A, 120-277V AC**

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, Polycarbonate, Pre-wired leads, Blue LED.	Ivory	<b>DSL120IL</b>	—	<b>DSL320IL</b>	—
	White	<b>DSL120ILW</b>	—	<b>DSL320ILW</b>	—

**Pilot, Light On with Load On 20A, 120-277V AC**

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, Polycarbonate, Pre-wired leads, Red LED.	Red	<b>DSL120PL</b>	—	—	—

Note: See page D-13 for accessories.  
See page D-15 for wallplates.  
See page D-20 for technical information.


**HP Conversion Chart**

	120V	208V	240V	277V AC
<b>15A</b>	.5HP	1.5HP	2HP	2HP
<b>20A</b>	1HP	2HP	2HP	2HP

Dimensions in Inches (mm)

**Specification Grade Commercial Series,  
15A, 120-277V AC**


Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	<b>CSB115AL</b>	<b>CSB215AL</b>	<b>CSB315AL</b>	<b>CSB415AL</b>
	Black	<b>CSB115BK</b>	<b>CSB215BK</b>	<b>CSB315BK</b>	<b>CSB415BK</b>
	Brown	<b>CSB115</b>	<b>CSB215</b>	<b>CSB315</b>	<b>CSB415</b>
	Gray	<b>CSB115GY</b>	<b>CSB215GY</b>	<b>CSB315GY</b>	<b>CSB415GY</b>
	Ivory	<b>CSB115I</b>	<b>CSB215I</b>	<b>CSB315I</b>	<b>CSB415I</b>
	Light Almond	<b>CSB115LA</b>	<b>CSB215LA</b>	<b>CSB315LA</b>	<b>CSB415LA</b>
	White	<b>CSB115W</b>	<b>CSB215W</b>	<b>CSB315W</b>	<b>CSB415W</b>


**Specification Grade Commercial Series,  
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, back and side wired.	Almond	<b>CSB120AL</b>	<b>CSB220AL</b>	<b>CSB320AL</b>	<b>CSB420AL</b>
	Black	<b>CSB120BK</b>	<b>CSB220BK</b>	<b>CSB320BK</b>	<b>CSB420BK</b>
	Brown	<b>CSB120</b>	<b>CSB220</b>	<b>CSB320</b>	<b>CSB420</b>
	Gray	<b>CSB120GY</b>	<b>CSB220GY</b>	<b>CSB320GY</b>	<b>CSB420GY</b>
	Ivory	<b>CSB120I</b>	<b>CSB220I</b>	<b>CSB320I</b>	<b>CSB420I</b>
	Light Almond	<b>CSB120LA</b>	<b>CSB220LA</b>	<b>CSB320LA</b>	<b>CSB420LA</b>
	Red	<b>CSB120R</b>	<b>CSB220R</b>	<b>CSB320R</b>	<b>CSB420R</b>
	White	<b>CSB120W</b>	<b>CSB220W</b>	<b>CSB320W</b>	<b>CSB420W</b>

**Specification Grade Commercial Series,  
15A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, side wired only.	Almond	<b>CS115AL</b>	—	<b>CS315AL</b>	—
	Black	<b>CS115BK</b>	—	<b>CS315BK</b>	—
	Brown	<b>CS115</b>	—	<b>CS315</b>	—
	Gray	<b>CS115GY</b>	—	<b>CS315GY</b>	—
	Ivory	<b>CS115I</b>	—	<b>CS315I</b>	—
	Light Almond	<b>CS115LA</b>	—	<b>CS315LA</b>	—
	White	<b>CS115W</b>	—	<b>CS315W</b>	—


**Specification Grade Commercial Series,  
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Toggle, side wired only.	Almond	<b>CS120AL</b>	—	<b>CS320AL</b>	—
	Black	<b>CS120BK</b>	—	<b>CS320BK</b>	—
	Brown	<b>CS120</b>	—	<b>CS320</b>	—
	Gray	<b>CS120GY</b>	—	<b>CS320GY</b>	—
	Ivory	<b>CS120I</b>	—	<b>CS320I</b>	—
	Light Almond	<b>CS120LA</b>	—	<b>CS320LA</b>	—
	White	<b>CS120W</b>	—	<b>CS320W</b>	—

Note: See page D-9 for pre-wired/leaded devices.  
See page D-13 for accessories.  
See page D-15 for wallplates.  
See page D-20 for technical information.

**HP Conversion Chart**

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP

Dimensions in Inches (mm)




### Style Line® Decorator Series Specification Grade, 15A, 120-277V AC

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, back and side wired.	Almond	<b>DS115AL</b>	—	<b>DS315AL</b>	—
	Black	<b>DS115BK</b>	—	<b>DS315BK</b>	—
	Brown	<b>DS115</b>	—	<b>DS315</b>	—
	Gray	<b>DS115GY</b>	—	<b>DS315GY</b>	—
	Ivory	<b>DS115I</b>	—	<b>DS315I</b>	—
	Light Almond	<b>DS115LA</b>	—	<b>DS315LA</b>	—
	Office White	<b>DS115OW</b>	—	<b>DS315OW</b>	—
	White	<b>DS115W</b>	—	<b>DS315W</b>	—


### Style Line® Decorator Series Specification Grade, 20A, 120-277V AC

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, back and side wired.	Almond	<b>DS120AL</b>	<b>DS220AL</b>	<b>DS320AL</b>	<b>DS420AL</b>
	Black	<b>DS120BK</b>	<b>DS220BK</b>	<b>DS320BK</b>	<b>DS420BK</b>
	Brown	<b>DS120</b>	<b>DS220B</b>	<b>DS320</b>	<b>DS420</b>
	Gray	<b>DS120GY</b>	<b>DS220GY</b>	<b>DS320GY</b>	<b>DS420GY</b>
	Ivory	<b>DS120I</b>	<b>DS220I</b>	<b>DS320I</b>	<b>DS420I</b>
	Light Almond	<b>DS120LA</b>	<b>DS220LA</b>	<b>DS320LA</b>	<b>DS420LA</b>
	Office White	<b>DS120OW</b>	<b>DS220OW</b>	<b>DS320OW</b>	<b>DS420OW</b>
	Red	<b>DS120R</b>	<b>DS220R</b>	<b>DS320R</b>	<b>DS420R</b>
	White	<b>DS120W</b>	<b>DS220W</b>	<b>DS320W</b>	<b>DS420W</b>



### Style Line® Decorator Series Specification Grade, Illuminated, Light On with Load Off 20A, 120-277V AC

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, with Blue LED, back and side wired.	Black	<b>DS120ILBK</b>	—	<b>DS320ILBK</b>	—
	Ivory	<b>DS120IL</b>	—	<b>DS320IL</b>	—
	White	<b>DS120ILW</b>	—	<b>DS320ILW</b>	—



### Style Line® Decorator Series Specification Grade, Pilot, Light On with Load On 20A, 120-277V AC

Description	Rocker Color	Single Pole	Double Pole	Three Way	Four Way
Rocker, with Red LED, back and side wired.	Black	<b>DS120PLBK</b>	—	—	—
	Ivory	<b>DS120PL</b>	—	—	—
	White	<b>DS120PLW</b>	—	—	—

Note: See page D-9 for pre-wired/leaded devices.

See page D-13 for accessories.


See page D-15 for wallplates.

See page D-20 for technical information.

#### HP Conversion Chart

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP

Dimensions in Inches (mm)



HBL18221CN

**HBL® Extra Heavy Duty Industrial Series  
15A, 347V AC**




Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle, back and side wired.	Brown	<b>HBL18201CN</b>	—	<b>HBL18203CN</b>	—
	Ivory	<b>HBL18201ICN</b>	—	<b>HBL18203ICN</b>	<b>HBL18204ICN</b>
Locking.		<b>HBL18201LCN</b>	—	<b>HBL18203LCN</b>	—
Key for Locking switch.		<b>HBL1209*</b>			

**HBL® Extra Heavy Duty Industrial Series  
20A, 347V AC**



Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon toggle, back and side wired.	Brown	<b>HBL18221CN</b>	—	<b>HBL18223CN</b>	—
	Ivory	<b>HBL18221ICN</b>	—	<b>HBL18223ICN</b>	<b>HBL18224ICN</b>



HBL1281


**PresSwitch® Specification Grade Push Button, Standard Type  
20A, 120-277V AC**



Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon actuator, side wired only.	Brown	<b>HBL1281</b>	<b>HBL1282</b>	<b>HBL1283*</b>	<b>HBL1284*</b>
	Ivory	<b>HBL1281I</b>	<b>HBL1282I</b>	<b>HBL1283I*</b>	<b>HBL1284I*</b>

**Momentary Type®  
20A, 120-277V AC**

Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Circuit normally closed, side wired only.	Brown	<b>HBL1281MC*</b>	—	—	—
Circuit normally open, side wired only.	Brown	<b>HBL1281MO*</b>	—	—	—



HBL1297

**Illuminated and Pilot Light PresSwitch®,  
120V AC Lighted Actuator, Light On with Load Off•**



Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
15A, nylon actuator.	Ivory	—	—	—	<b>HBL1259I*</b>
20A, nylon actuator.	Ivory	<b>HBL1287I</b>	—	<b>HBL1288I*</b>	—

**Pilot Light Actuator, Light On with Load On  
20A, 120V AC**



Description	Toggle Color	Single Pole	Double Pole	Three Way	Four Way
Nylon actuator.	Red	<b>HBL1297</b>	—	<b>HBL1298*</b>	—

Note: Keys are supplied with each locking switch. For extra keys order HBL1209.

\*Not UL Listed, CSA Certified.

•Not HP rated.

See page D-13 for accessories.

See page D-15 for wallplates.

See page D-20 for technical information.

**HP Conversion Chart**

	120V	208V	240V	277V AC
15A	.5HP	1.5HP	2HP	2HP
20A	1HP	2HP	2HP	2HP
30A	2HP	2HP	2HP	2HP

Dimensions in Inches (mm)



# Switches Accessories

Pilot Light, SWITCHOUT® Lockout Device and Weatherproof Switch Plates for Toggle Switches



## Pilot Light, 120-277V AC

Description	Catalog Number
Red neon pilot light, back and side wired, fits standard switch plate.	<b>HBL1220RJ</b>

**IP44**  
SUITABILITY



**HBL1220RJ**

## Brass Locking Attachment for Switches Available in Master Keying and Straight Keying Systems

Description	Catalog Number
Straight keying (all locks alike). Appropriate for most applications. Straight cylinder type lock, each HBL96061 ordered operates on the same key. All locks are keyed alike.	<b>HBL96061*</b>
Same as above except in dull chrome finish to match stainless steel plates.	<b>HBL96061DCH*</b>



**HBL96061**  
shown with wallplate and switch (sold separately)

Straight keying (individual). Straight cylinder type lock, each HBL96062 ordered operates on a different key. All locks are keyed differently and individually. This type cannot be master keyed.	<b>HBL96062*</b>
------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	------------------

## SWITCHOUT® Lockout Device

Description	Catalog Number
Yellow, nylon toggle switch lockout device (Two devices per package).	<b>HSLDPK2*</b>

## Weatherproof Plates

Description	Catalog Number
Clear bubble plate, silicone rubber for use with all general purpose AC toggle and PresSwitch® switches. Fits both FS/FD and standard boxes.	<b>HBL1795</b>
Cast aluminum lift cover plate with fiber shield. For standard toggle and PresSwitch®. Fits only FS/FD boxes.	<b>HBL7420</b>



**HSLDPK2**


## Weatherproof Plates for PresSwitch®

Description	Catalog Number
Gray neoprene PresSwitch® plate. Fits FS/FD and standard boxes.	<b>HBL1750</b>
Same as above except yellow.	<b>HBL17CM50</b>
Gray neoprene PresSwitch® plate with 125V red pilot light. Fits only FS/FD boxes.	<b>HBL1785</b>
Same as above except yellow.	<b>HBL17CM85</b>




Note: \*Not UL Listed or CSA Certified.


Each locking wallplate is supplied with two keys.  
See section Z for additional information on safety lockout devices.  
See section N for additional wallplates.




**HBL1795**



**HBL1785**



**HBL1750**



**HBL7420**

Dimensions in Inches (mm)



**UL, CSA, and Fed. Spec. Listing Data**

Catalog Number	WS896 Listed	UL Listed UL20	CSA Certified	Catalog Number	WS896 Listed	UL Listed UL20	CSA Certified
1201	Yes	Yes	Yes	HBL1224	Yes	Yes	Yes
1203	Yes	Yes	Yes	HBL1221L	Yes	Yes	Yes
1221	Yes	Yes	Yes	HBL1222L	Yes	Yes	Yes
1222	Yes	Yes	Yes	HBL1223L	Yes	Yes	Yes
1223	Yes	Yes	Yes	HBL1224L	Yes	Yes	Yes
1224	Yes	Yes	Yes	HBL1221IL	Yes	Yes	Yes
1221PW	Yes	Yes	Yes	HBL1223IL	Yes	Yes	Yes
1222PW	Yes	Yes	Yes	HBL1221PL	Yes	Yes	Yes
1223PW	Yes	Yes	Yes	HBL1222PL	Yes	Yes	Yes
1224PW	Yes	Yes	Yes	HBL1223PL	Yes	Yes	Yes
CS115	Yes	Yes	Yes	HBL1221RKL	No	Yes	Yes
CS315	Yes	Yes	Yes	HBL1222RKL	No	Yes	Yes
CS120	Yes	Yes	Yes	HBL1223RKL	No	Yes	Yes
CS320	Yes	Yes	Yes	HBL1224RKL	No	Yes	Yes
CSB115	Yes	Yes	Yes	HBL1259I	No	No	No
CSB215	Yes	Yes	Yes	HBL1281	No	Yes	Yes
CSB315	Yes	Yes	Yes	HBL1282	No	Yes	Yes
CSB415	Yes	Yes	Yes	HBL1283	No	No	No
CSB120	Yes	Yes	Yes	HBL1284	No	No	No
CSB220	Yes	Yes	Yes	HBL1287I	No	Yes	Yes
CSB320	Yes	Yes	Yes	HBL1288I	No	No	No
CSB420	Yes	Yes	Yes	HBL1281MO	No	No	No
CSL115	Yes	Yes	Yes	HBL1281MC	No	No	No
CSL215	Yes	Yes	Yes	HBL1297	No	Yes	Yes
CSL315	Yes	Yes	Yes	HBL1298	No	No	No
CSL415	Yes	Yes	Yes	HBL1381	No	Yes	Yes
CSL120	Yes	Yes	Yes	HBL1382	No	Yes	Yes
CSL220	Yes	Yes	Yes	HBL1385	No	Yes	Yes
CSL320	Yes	Yes	Yes	HBL1386	No	Yes	Yes
CSL420	Yes	Yes	Yes	HBL1386L	No	Yes	Yes
DS115	No	Yes	Yes	HBL1388	No	Yes	Yes
DS315	No	Yes	Yes	HBL1556	No	Yes	Yes
DS120	No	Yes	Yes	HBL1557	No	Yes	Yes
DS220	No	Yes	Yes	HBL1556L	No	Yes	Yes
DS320	No	Yes	Yes	HBL1557L	No	Yes	Yes
DS420	No	Yes	Yes	HBL3031	Yes	Yes	Yes
DS120IL	No	Yes	Yes	HBL3032	Yes	Yes	Yes
DS320IL	No	Yes	Yes	HBL3033	Yes	Yes	Yes
DS120PL	No	Yes	Yes	HBL3031PL	Yes	Yes	Yes
DSL115	No	Yes	Yes	HBL3031PL	Yes	Yes	Yes
DSL215	No	Yes	Yes	HBL3032PL	Yes	Yes	Yes
DSL315	No	Yes	Yes	SNAP1201	No	Yes	Yes
DSL415	No	Yes	Yes	SNAP1201IL	No	Yes	Yes
DSL120	No	Yes	Yes	SNAP1201PL	No	Yes	Yes
DSL220	No	Yes	Yes	SNAP1203	No	Yes	Yes
DSL320	No	Yes	Yes	SNAP1203IL	No	Yes	Yes
DSL420	No	Yes	Yes	SNAP1221	No	Yes	Yes
HBL1201	Yes	Yes	Yes	SNAP1221IL	No	Yes	Yes
HBL1202	Yes	Yes	Yes	SNAP1221PL	No	Yes	Yes
HBL1203	Yes	Yes	Yes	SNAP1223	No	Yes	Yes
HBL1204	Yes	Yes	Yes	SNAP1223	No	Yes	Yes
HBL1201IL	Yes	Yes	Yes	SNAP1223IL	No	Yes	Yes
HBL1203IL	Yes	Yes	Yes	SNAP2101	No	Yes	Yes
HBL1201PL	Yes	Yes	Yes	SNAP2101IL	No	Yes	Yes
HBL1203PL	Yes	Yes	Yes	SNAP2101PL	No	Yes	Yes
HBL1201L	Yes	Yes	Yes	SNAP2103	No	Yes	Yes
HBL1202L	Yes	Yes	Yes	SNAP2103IL	No	Yes	Yes
HBL1203L	Yes	Yes	Yes	SNAP2121	No	Yes	Yes
HBL1204L	Yes	Yes	Yes	SNAP2121IL	No	Yes	Yes
HBL1221	Yes	Yes	Yes	SNAP2121PL	No	Yes	Yes
HBL1222	Yes	Yes	Yes	SNAP2123	No	Yes	Yes
HBL1223	Yes	Yes	Yes	SNAP2123IL	No	Yes	Yes

Note: Catalog numbers above represent all colors and variations, per NEMA® WD-1 requirements.

NEMA® is a registered trademark of the National Electrical Manufacturers Association.



1-Gang



2-Gang



3-Gang

### Standard Size, Smooth Nylon, Toggle Switch Plates

Color	Catalog Number		
Almond	<b>NP1AL</b>	<b>NP2AL</b>	<b>NP3AL</b>
Black	<b>NP1BK</b>	<b>NP2BK</b>	<b>NP3BK</b>
Brown	<b>NP1</b>	<b>NP2</b>	<b>NP3</b>
Gray	<b>NP1GY</b>	<b>NP2GY</b>	<b>NP3GY</b>
Ivory	<b>NP1I</b>	<b>NP2I</b>	<b>NP3I</b>
Light Almond	<b>NP1LA</b>	<b>NP2LA</b>	<b>NP3LA</b>
Office White	<b>NP1OW</b>	<b>NP2OW</b>	<b>NP3OW</b>
Red	<b>NP1R</b>	<b>NP2R</b>	—
White	<b>NP1W</b>	<b>NP2W</b>	<b>NP3W</b>

### Standard Size, Smooth Metal, Toggle Switch Plates


Color	Catalog Number		
Aluminum	<b>SA1</b>	<b>SA2</b>	①
Brass	<b>SB1</b>	<b>SB2</b>	<b>SBP3*</b>
Stainless Steel, 302/304	<b>SS1</b>	<b>SS2</b>	<b>SS3</b>
Stainless Steel, 430	<b>SS1L</b>	<b>SS2L</b>	<b>SS3L</b>



1-Gang



2-Gang



3-Gang

### Standard Size, Smooth Nylon, Style Line® Switch Plates

Color	Catalog Number		
Almond	<b>NP26AL</b>	<b>NP262AL</b>	<b>NP263AL</b>
Black	<b>NP26BK</b>	<b>NP262BK</b>	<b>NP263BK</b>
Brown	<b>NP26</b>	<b>NP262</b>	<b>NP263</b>
Gray	<b>NP26GY</b>	<b>NP262GY</b>	<b>NP263GY</b>
Ivory	<b>NP26I</b>	<b>NP262I</b>	<b>NP263I</b>
Light Almond	<b>NP26LA</b>	<b>NP262LA</b>	<b>NP263LA</b>
Office White	<b>NP26OW</b>	<b>NP262OW</b>	<b>NP263OW</b>
Red	<b>NP26R</b>	<b>NP262R</b>	<b>NP263R</b>
White	<b>NP26W</b>	<b>NP262W</b>	<b>NP263W</b>


### Standard Size, Smooth Metal, Style Line® Switch Plates

Color	Catalog Number		
Aluminum	①	①	①
Brass	<b>SB26</b>	<b>SB262</b>	①
Stainless Steel, 302/304	<b>SS26</b>	<b>SS262</b>	<b>SS263</b>
Stainless Steel, 430	<b>SS26L</b>	<b>SS262L</b>	—


Note: See section N for additional wallplates.

\*Brass plated.

① Available as a custom metal wallplate. See section N for additional information.




600 and 1000W Dimmer  
Fits Single-Gang Wall Boxes.  
**AS63 and AS103**



1500 and 2000W Dimmer  
Fits Single-Gang Wall Boxes.  
**AS153 and AS203**



600 and 1000W Dimmer  
Fits Single-Gang Wall Boxes.  
**AR61 and AR101**



1500 and 2000W Dimmer  
Fits Single-Gang Wall Boxes.  
**AR151 and AR201**

### Architectural Grade, Incandescent Preset Slide Control Dimmers

Description	Color	Rating	Catalog Number
Single pole/three way - preset.	White	600W, 120V AC, 60Hz	<b>AS63</b>
Single pole/three way - preset.	White	1000W, 120V AC, 60Hz	<b>AS103</b>
Single pole/three way - preset.	White	1500W, 120V AC, 60Hz	<b>AS153</b>
Single pole/three way - preset.	White	2000W, 120V AC, 60Hz	<b>AS203</b>

### Accessories

Description	Color	Catalog Number
Small plate kit for 600W and 1000W models.	Ivory	<b>AS1I</b>
Includes non-metallic trimplate and slide.	White	<b>AS1W</b>
Large plate kit for 1500W and 2000W models.	Ivory	<b>AS2I</b>
Includes non-metallic trimplate and slide.	White	<b>AS2W</b>

Note: The dimmers listed above can be wired for single pole or three way applications.  
See page D-17 for ganging and derating.

### Architectural Grade, Incandescent Rotary Control Dimmers

Description	Color	Rating	Catalog Number
Single pole - push on/off.	Beige	600W, 120V AC, 60Hz	<b>AR61</b>
Three way - push on/off.	Beige		<b>AR63</b>
Single pole - push on/off.	Beige	1000W, 120V AC, 60Hz	<b>AR101</b>
Three way - push on/off.	Beige		<b>AR103</b>
Single pole, rotary on/off.	Beige	1500W, 120V AC, 60Hz	<b>AR151</b>
Single pole, rotary on/off.	Beige	2000W, 120V AC, 60Hz	<b>AR201</b>

### Accessories

Description	Color	Catalog Number
Small plate kit for 600W and 1000W models.	Beige	<b>AR1BE</b>
Includes non-metallic trimplate and knob.	White	<b>AR1W</b>
Large plate kit for 1500W and 2000W models.	Beige	<b>AR2BE</b>
Includes non-metallic trimplate and knob.	White	<b>AR2W</b>

Note: See page D-17 for ganging and derating.






## Architectural Grade Slide and Rotary Series Number of Switchboxes Required with Dimmer Side sections Intact

		Number of Small Controls (600W and 1000W)						
		0	1	2	3	4	5	6
Number of Large Controls (1500W and 2000W)	0	0	1	1+1	4	1+4	7	1+7
	1	1	3	5	6	8	9	11
	2	4	6	7	9	10	12	13
	3	6	8	10	11	13	14	16
	4	9	11	12	14	15	17	18

Number of Gangs Required

Note: When ganging an even number of small controls with no side sections removed (plus numbers in chart), use gangable switchboxes with tapped ears as shown below. Do not use plaster rings or gangbox covers. Space an additional switchbox 3/4 in. apart from the other switchbox(es). A 3/4 in. close nipple is recommended as a spacer between the switchboxes.

### Example of 4-Gang Installation




## Number of Switchboxes Required with Side Sections Removed

		Number of Small Controls (600W and 1000W)						
		0	1	2	3	4	5	6
Number of Large Controls (1500W and 2000W)	0	0	1	2	3	4	5	6
	1	1	3	4	5	6	7	8
	2	3	5	6	7	8	9	10
	3	5	7	8	9	10	11	12
	4	7	9	10	11	12	13	14

Number of Gangs Required

Note: When removing side sections, remove only inner side sections. Do not remove side sections on outer ends of gang. The same installation rules apply to rotary dimmers (not shown).



## Derating Chart

No side sections removed	One side section removed	Both side sections removed
600W	600W	500W
1000W	900W	700W
1500W	1250W	1000W
2000W	1800W	1500W

Note: When ganging any combination of small and large controls, place a small control on one extreme end of the gang, and a large control at the other end of the gang. When ganging with side sections intact, use offset mounting holes. When ganging with side sections removed, use center mounting holes. Allow a 1/2 in. gap (space) between controls for ease in attaching the faceplate.

## Specification Grade Slide and Rotary Series Switchboxes Required: Side sections removed

### Derating Chart

1 dimmer in wall box	2 dimmers in wall box	3 or more dimmers in wall box
600W	500W	400W
1000W	800W	650W
5A fan speed	4A fan speed	3A fan speed



HBL11



HBL123SP

### 10A 250V AC 20A 125V AC Horsepower Rated 3/4 HP, 125-250V AC

Description		Terminal	Catalog Number
Single pole/ single throw.		Screw Spade	<b>HBL11</b> <b>HBL11SP</b>
Single pole/ single throw momentary.		Screw Spade	<b>HBL11M</b> <b>HBL11SPM</b>
Single pole/ double throw.		Screw Spade	<b>HBL12</b> <b>HBL12SP</b>
Single pole/ double throw 3-position center off.		Screw Spade	<b>HBL123</b> <b>HBL123SP</b>
Single pole/ double throw 3-position center off momentary.		Screw Spade	<b>HBL123MM</b> <b>HBL123SPMM</b>

Note: All threaded stems 1/2 in.-32 thread.

### 10A 240V AC 15A 120V AC

Description		Terminal	Catalog Number
Single pole/ single throw.		Screw	<b>HBL118</b>

Note: 1/2 in.-32 thread.

### 4A 250V 8A 125V 10A 120V AC 1/3 HP 120V AC

Description		Terminal	Catalog Number
Single pole/ single throw.		#18 Std. AWG Copper Wire Leads 105° C Black.	<b>HBL11WL</b>

Note: 1/2 in.-32 thread, keyway .080 x .035.

### Specifications

Impact Resistant Thermoplastic Body.

Fine Silver Contacts.

Knurled Nut, Hex Nut And Strap All Nickel Plated.

Keyed Brass Bushing Nickel Plated.

Brass Toggle Nickel Plated.

Choice of Terminal Design: .250 in. (6.3) Male Tab Spade Type or 6/32 Screw Type.

UL Recognized.

Dimensions in Inches (mm)





# Switches

## Heavy Duty Panel Mount

Panel Mount and Bat Handle Switches



### 10A 250V AC 20A 125V AC Horsepower Rated 1½ HP, 125-250V AC

Description	Terminal	Catalog Number
Double pole/ single throw. 	Screw Spade	<b>HBL21</b> <b>HBL21SP</b>
Double pole/ single throw. 	Screw Spade	<b>HBL22</b> <b>HBL22SP</b>
Double pole/ double throw 3-position center off. 	Screw Spade	<b>HBL223</b> <b>HBL223SP</b>
Double pole/ double throw 3-position center off momentary. 	Screw Spade	<b>HBL223MM</b> <b>HBL223SPMM</b>
Silicone rubber boot.	Screw Spade	<b>SSB1</b>



HBL21




HBL223



SSB1

Note: All threaded stems 1/32 in.-32 thread.  
See Y-33 for information on 12V DC tapered handle switches.

### 4A 250V 8A 125V 10A 120V AC 1/3 HP 120V AC

Description	Terminal	Catalog Number
Single pole/ single throw. 	#18 Std. AWG Copper Wire Leads 105° C Black.	<b>HBL11PBWL</b>




HBL11PBWL

Note: 1/32 in.-32 thread, keyway .080 x .035.


Dimensions in Inches (mm)




## Standard Toggle Type Switches




## Illuminated Switches (light on with load off)




## Pilot Light Switches (light on with load on)



## Three Way Pilot Switches



## Three Position Switches, Momentary and Maintained



## Specifications - HBL® Extra Heavy Duty Industrial Grade Switches (SP, DP, 3-Way, 4-Way)

Listings	Component	Material
UL Listed	Base	Thermoset, Color Coded by Amperage
CSA Certified	Top	Thermoset, Gray
Verified to Fed. Spec. W-S-896,	Toggle	Nylon
SP, DP, 3-way and 4-way	Terminals	Brass
	Terminal Screws	Brass
	Mounting Bridge	Nickel Plated Steel
	Contacts	Silver Alloy
	Moveable Contact Arm	Brass
	Rocker	Elastomer
	Ground Terminal	Nickel-Plated Steel
	Ground Screw	Brass
	Automatic Grounding Clip	Stainless Steel

## Performance Data

Electrical	
Dielectric Voltage	Withstands 1500V AC minimum for 1 minute.
Max. Working Voltage	277V AC.
Overload	Minimum 4.8 times rated current for 100 cycles.
Temperature Rise	30°C maximum at rated current.
Max. Continuous Current	15A, 20A, 30A.
Endurance	50,000 cycles min., tungsten filament lamp load Fed. Spec. #WS896, SP, DP, 3-way and 4-way.
Mechanical	
Terminal Accommodations	#14 AWG min. - #10 AWG max. solid and stranded copper wire only.
Environmental	
Flammability	UL 94V-2.
Operating Temperature	Max. continuous: 75°C; Min. continuous: -40°C without impact.