



Height Master Series 515

Series 515

Features

- Models with staggered arrangement of block stack have two measuring faces on the same level, one facing up and the other down (except for **515-310**).
- Each Height Master is supplied with a gage block for zero-setting.
- Supplied in fitted wooden case.

Technical Data

Graduation: .00001" or 0.001mm

Counter resolution: .001" or 0.01mm

Character Height: .16" / 4mm

Micrometer Head

Travel stroke: 1" or 20mm

Pitch: .025"/rev or 0.5mm/rev

Hysteresis: .00004" or 1µm

Provided with inspection certificate.

Standard Accessories

Reference Block: 11mm for 515-322

Reference Block: .3" for 515-310, 515-311

Optional Accessories

515-112: Auxiliary block kit for bore gage (mm)

515-119: Auxiliary block kit for bore gage (for **515-310**)

515-121: Auxiliary block kit for bore gage (for **515-311**)



Order No	515-310	515-311
Range Inch	.2-12.5"	.2-12.5"
Block Step	.5(straight)"	1(staggered)"
Graduation	.00001"	.00001"
Block Pitch Accuracy	.00005"	.00005"
Block Parallelism	.00004"	.00004"
Weight	47.1lbs. 23kg	50.6lbs. 23kg
Micrometer Head Accuracy	.00005"	.00005"