

MAX235H105S.079

OVERVIEW

- Waterproof and dustproof IP67 certified
- Watertight seal around lid
- Automatic pressure release valve
- Easy to open double throw latches
- Load tested soft grip handle
- Stackable interlocking system
- Thick body material
- Extra fixing points
- Fully length hinges
- Nylon pins, corrosion free
- Cubed foams in the bottom and convoluted foams in the lid available as standard
- Screen printing space and rectangular resin label space on the lid

Body and handle: polypropylene copolymer

Latches: nylon

Pins: nylon + 30% fiberglass

O-ring: polymer

COLOURS:



EXTERNAL DIMENSIONS: 258 x 243 x H117.5 mm (10.16 x 9.56 x H4.62 inch)

INTERNAL DIMENSIONS: 235 x 180 x H106 mm (9.25 x 7.08 x H4.17 inch)

LID-BOTTOM DEPTH: 25 + 81 mm (0.98 + 3.19 inch)

WEIGHT W/O FOAM: 0820 g

WEIGHT WITH FOAM: 0880 g

MOULDING: injection molded

RANGE TEMPERATURE: -30 / 90°C (-22 / 194°F)

FEATURES: IP67

CUSTOMIZATION: personalized nameplate/resin label

ACCESSORIES: cubed foams

