



Duplex Frames Fit Industry Standard Duplex Style Openings.

Frames Accept All Hubbell **XCELERATOR™** Jacks and Audio/Video Connectors.

IFP126OW (Style Line®) and IFP18OW are the Only Plates in the Industry that are UL Listed for Power and Low-Voltage with Label Fields.

## Duplex Plates and Outlet Frames



Provides application flexibility at the workstation.

TIA/EIA-606-A label fields.

Consistent color match.

### FEATURES

- Instant communication mounting capabilities within a rectangular (GFCI) or duplex electrical design.
- Frames delivery 2- to 4-port configurations, lending flexibility and increased capacity to the work area.
- Tamper-resistant, rear keystone mounting.
- Nylon plates virtually unbreakable.

### SPECIFICATIONS

- ◆ IFP plate material: UL 94V-0 rated flame-retardant.
- ◆ Metal plate material: brushed stainless steel, or solid, brushed brass.
- ◆ Frames are high-impact polymer construction.
- ◆ Tamper-resistant, flush keystone mounting.

### STANDARDS/LISTINGS/VERIFICATIONS

- UL and cUL listed.
- ANSI/TIA/EIA-606A station labeling capability.
- IFP126OW and IFP18OW are UL listed for power and low voltage data applications.
- Mounts to standard NEMA openings and boxes.

Duplex frames are ideal for applications where low voltage data connectivity is desired within any standard Duplex application. This solution makes installation easier and more cost-effective, particularly in retrofits of existing spaces.

Frames are available in 2- and 4-port capacities and provide media flexibility by accommodating Hubbell **XCELERATOR™** modular jacks and Audio/Video connectors and multimedia modules.

These frames are compatible with Hubbell Duplex cover plates to provide a contemporary finish and a consistent color match next to any Hubbell plate, module or surface mount box. Additionally, Duplex office white face plates include recessed label fields for TIA/EIA-606-A compliance.

### APPLICATIONS SUPPORTED

- ▲ Standard residential and commercial NEMA rectangular Duplex face plates.
- ▲ Fire-rated poke through with pedestal.
- ▲ **MEDIATRAK®** surface raceway.
- ▲ Service poles.
- ▲ In-floor boxes.
- ▲ Ideal for retrofit and Small Office/Home Office (SoHo) applications.

**ORDERING INFORMATION**

**Duplex 106 Outlet Frames**



BR106B

2-port



Q106O

4-port

Black	<b>BR106B</b>	<b>Q106B</b>
Electric Ivory	<b>BR106E</b>	<b>Q106E</b>
Gray	<b>BR106G</b>	<b>Q106G</b>
Office White	<b>BR106C</b>	<b>Q106O</b>
White	<b>BR106W</b>	<b>Q106W</b>

**Duplex and IFP Cover Plates**



HPWS82



IFP18OW

Color/Finish	Duplex Single-Gang	Duplex Double-Gang	IFP Duplex w/Label Fields Single-Gang
Black	<b>HPWP8BK</b>	<b>HPWP82BK</b>	-
Brass	<b>HPWB8</b>	<b>HPWB82</b>	-
Electric Ivory	<b>HPWP8EI</b>	<b>HPWP82EI</b>	-
Gray	<b>HPWP8GY</b>	<b>HPWP82GY</b>	-
Office White	<b>HPWP8OW</b>	<b>HPWP82OW</b>	<b>IFP18OW</b>
Stainless Steel	<b>HPWS8</b>	<b>HPWS82</b>	-
White	<b>HPWP8W</b>	<b>HPWP82W</b>	-

**ACCESSORIES**

**XCELERATOR™ Jacks, Category 6 and 5e**

Category	Catalog No.
Category 5e	<b>HXJ5EXX</b>
Category 6	<b>HXJ6XX</b>

XX = Color:

- 'AL' = Almond
- 'B' = Blue
- 'BK' = Black
- 'EI' = Electric Ivory
- 'GL25' = Gold\*
- 'GY' = Gray
- 'GN' = Green
- 'OW' = Office White
- 'OR' = Orange
- 'P25' = Purple\*
- 'R' = Red
- 'TI' = Telco Ivory
- 'W' = White
- 'Y' = Yellow

\* 25-packs only.



**Patch Cords, Category 6 and 5e**

Category	Catalog No.
Category 5e	<b>PCX5EXX*</b>
Category 6	<b>PCX6XX**</b>

XX = Standard Color:

- 'B' = Blue; 'BK' = Black;
- 'GY' = Gray; 'Y' = Yellow

For other colors replace color designation with one of the following:  
OR = Orange, R = Red, GN = Green, P = Purple, W = White

- \* = Standard Length: '01'=1'; '03'=3'; '05'=5'; '07'=7'; '10'=10'; '15'=15'; '20'=20'; '25'=25'; '30'=30'; '35'=35'; '40'=40'; '45'=45'; '50'=50'; '55'=55'; '60'=60'; '75'=75'; '100'=100'
- \*\* = Standard Length: '03' = 3'; '06' = 6'; '08' = 8'; '10' = 10'; '12' = 12'; '16' = 16'; '20' = 20'



**Audio/Video Connectors**

Description (Office White)	Catalog No.
Blank Module	<b>SFB10</b>
F-Type Coupler Bulkhead F/F	<b>SFFX</b>
RCA Solder Coupler (Red)	<b>SFRCR</b>
S-Video F/F Coupler (Black)	<b>SFSVBK</b>
SC Simplex, SM/MM	<b>SFSC</b>
ST Style, SM/MM	<b>SFST</b>



\* Consult the Full Line Catalog (pages B8-B11) for a complete listing of Hubbell's family of Audio/Video Connector options and colors.

**Hubbell Labeling Solutions\***

Face Plate Labels, white adhesive	<b>XPLFPA10W</b>
Face Plate Labels, white paper	<b>XPLFP10W</b>
Face Plate Labels, clear adhesive	<b>XPLFPA10C</b>
Port Icon Labels, white adhesive	<b>XPLIPA10W</b>
Port Icon Labels, clear adhesive	<b>XPLIPA10C</b>
<b>Pre-Printed Icon Label Booklets (5-packs)</b>	
Icon Labels, clear adhesive with black text	<b>XPICONS</b>
Icon Labels, clear adhesive with white text	<b>XPICONSW</b>

\* Contact our website at [www.hubbell-premise.com](http://www.hubbell-premise.com) for our unique Labeling Software.



**Hubbell Premise Wiring**

HUBBELL INCORPORATED (Delaware)  
14 Lord's Hill Road • Stonington, CT 06378-0901 • (860) 535-8326 • 800-626-0005  
Fax: (860) 535-8328 • Internet site: <http://www.hubbell-premise.com>

**Worldwide Locations**

Hubbell Premise Wiring, Asia Pacific	852-2836-7131	Fax: 852-2836-7132
Hubbell Canada Inc.	905-839-1138	Fax: 905-839-9108
Hubbell Premise Wiring, Central America	506-309-4158	Fax: 506-260-1616
Hubbell Premise Wiring, China	8621-6309-0119	Fax: 8621-6309-0122
Hubbell Premise Wiring, Colombia	571-245-8940	Fax: 571-340-0925
Hubbell Premise Wiring, Europe	44-01283 500500	Fax: 44-01283 500400
Hubbell Int'l. Inc., Korea Branch	82-2-(0)2607-1363	Fax: 82-2-(0)2603-7386

Hubbell Premise Wiring, Latin America	305-408-4501	Fax: 305-408-8201
Hubbell de Mexico, S.A. de C.V.	(5255) 9151-9999	Fax: (5255) 9151-9989
Hubbell Premise Wiring, Middle East	971-4-393-4192	Fax: 971-4-393-4194
Hubbell-Taian Co., Ltd., Taiwan	886-2-2522-1862	Fax: 886-2-2522-1872
Hubbell Premise Wiring, Turkey	90-216-313-5016	Fax: 90-216-414-8148
Hubbell Premise Wiring, Venezuela	58-416-680-7453	Fax: 58-281-274-7900