

Capacitor, Ceramic, SMD, MLCC, Temperature Stable, Automotive Grade, 0.22 uF, +/-10% Tol, 50 V, X7R, 1206 (3216 metric)



| General Information | |
|--------------------------|---|
| Supplier: | KEMET |
| Application: | Automotive (AEC-Q200 Qualified) |
| Chip Size: | 1206 (3216 metric) |
| Temperature Coefficient: | X7R |
| Part Type Description: | SMD, MLCC, Temperature Stable, Automotive Grade |
| Termination Type: | Tin (Sn) |
| Marked: | No |
| RoHS: | Yes |

| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 3.2 | +/-0.2 |
| W | 1.6 | +/-0.2 |
| T | 0.9 | +/-0.10 |
| B | 0.5 | +/-0.25 |

| Packaging Specifications | |
|--------------------------|--------------|
| Package Kind: | T&R |
| Package Size: | 7 in/180 mm |
| Package Type: | Plastic Tape |
| Package Quantity: | 4000 |

| Specifications | |
|------------------------|--|
| Capacitance: | 0.22 uF |
| Voltage: | 50 V |
| Tolerance: | +/-10% |
| Temperature Range: | -55/+125C |
| Dissipation Factor: | 2.5% |
| Failure Rate: | N/A |
| Aging Rate: | 3% loss/decade hour |
| Insulation Resistance: | 2.27 GOhm |
| Dielectric Strength: | 125 V |
| Miscellaneous: | Note: Referee time for X7R dielectric for this part number is 1000 hours |