

Capacitor, Ceramic, SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade, 8200 pF, +/-5% Tol, 50 V, COG, 1210 (3225 metric)



General Information	
Supplier:	KEMET
Application:	Automotive (AEC-Q200 Qualified)
Chip Size:	1210 (3225 metric)
Temperature Coefficient:	COG
Part Type Description:	SMD, MLCC, FT-CAP, Ultra-Stable, Auto Grade
Termination Type:	Flexible Termination
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	3.3	+/-0.4
W	2.6	+/-0.3
T	0.9	+/-0.20
B	0.6	+/-0.25

Packaging Specifications	
Package Kind:	T&R
Package Size:	7 in/180 mm
Package Type:	Plastic Tape
Package Quantity:	4000

Specifications	
Capacitance:	8200 pF
Voltage:	50 V
Tolerance:	+/-5%
Temperature Range:	-55/+125C
Dissipation Factor:	0.1%
Failure Rate:	N/A
Aging Rate:	0% loss/decade hour
Insulation Resistance:	100 GOhm
Dielectric Strength:	125 V
Miscellaneous:	Note: KEMET 50V rated parts may be operated at 63 Volts