

Capacitor, Ceramic, SMD, MLCC, High Temperature, Class II, 0.15 uF, +/-10% Tol, 25 V, X7R, 0603 (1608 metric)



General Information	
Supplier:	KEMET
Application:	175C
Chip Size:	0603 (1608 metric)
Temperature Coefficient:	X7R
Part Type Description:	SMD, MLCC, High Temperature, Class II
Termination Type:	Tin (Sn)
Marked:	No
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	1.6	+/-0.15
W	0.8	+/-0.15
T	0.8	+/-0.07
B	0.35	+/-0.15
S	0.7	MIN

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	1

Specifications	
Capacitance:	0.15 uF
Voltage:	25 V
Tolerance:	+/-10%
Temperature Range:	-55/+175C
Dissipation Factor:	3.5%
Failure Rate:	N/A
Aging Rate:	3% loss/decade hour
Insulation Resistance:	3.33 GOhm
Dielectric Strength:	62.5 V
Miscellaneous:	Note: Referee time for X7R dielectric for this part number is 1000 hours