

Capacitor, film, Metallized Polyester, 0.01 uF, +/-10% Tol, -55/+105C, General Purpose, 1000 VDC@85C, Lead Spacing=15 mm



General Information	
Supplier:	KEMET
Dielectric:	Metallized Polyester
Application:	General Purpose
Sub Application:	AEC-Q200
Style:	Radial Box
Lead Form:	Wire Leads
Features:	Pulse
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	18	+0.2
H	11	+1
T	5	+0.2
S	15	+/-0.4
LL	25	+2/-1
F	0.8	+/-0.05

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	1000

Specifications	
Capacitance:	0.01 uF
Voltage:	1000 VDC
Tolerance:	+/-10%
Voltage AC:	250 VAC
Rated Temperature:	85C
Temperature Range:	-55/+105C
Dissipation Factor @ 1 kHz:	1%
Dissipation Factor @ 10 kHz:	1.5%
Insulation Resistance:	30 GOhm
Inductance:	10
Maximum dVdT:	30 v/us
Miscellaneous:	Upper Operating Temperature Of 125C Is Allowed For A Maximum Operating Time Of 1,000 Hours. Above 85C, DC And AC Voltage Derating Is 1.25%/C.