


Capacitor, Tantalum, SMD, Polymer, Molded, Low ESR, Non-Combustible, 68 uF, 7343, +/-20% Tol, 16 VDC (105C)



General Information

Supplier:	KEMET
Application:	Low ESR
Sub Application:	(NonCombustibleCathode)
Part Type Description:	SMD, Polymer, Molded, Low ESR, Non-Combustible
Construction:	Standard Chip-Polymer
Body Type:	SMD Chip
Footprint:	7343
Weight:	434.83 mg
RoHS:	Yes

Dimensions (mm)

Symbol	Dimension	Tolerance
L	7.3	+/-0.3
W	4.3	+/-0.3
H	2.8	+/-0.3
F	2.4	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	3.6	MIN

Specifications

Capacitance:	68 uF
Tolerance:	+/-20%
Voltage:	16 VDC (105C)
Temperature Range:	-55/+105C
Current/Ripple Current:	2100 mAmps (100kHz 45C)
Current/Ripple Current:	1470 mAmps (85C)
Current/Ripple Current:	997.5 mAmps (105C)
Resistance/ESR:	50 mOhms (100kHz 25C)
Failure Rate:	N/A
Leakage Current:	108.8 uA
Dissipation Factor:	10%

Packaging Specifications

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500