

**KEMET Part Number: T491X106K050AT**  
(B45196H7106K509)

Capacitor, Tantalum, SMD, MnO2, Molded, 10 uF, 7343, +/-10% Tol, 50 VDC (85C)



| Dimensions (mm) |           |           |
|-----------------|-----------|-----------|
| Symbol          | Dimension | Tolerance |
| L               | 7.3       | +/-0.3    |
| W               | 4.3       | +/-0.3    |
| H               | 4         | +/-0.3    |
| F               | 2.4       | +/-0.1    |
| S               | 1.3       | +/-0.3    |
| B               | 0.5       | +/-0.15   |
| X               | 0.1       | +/-0.1    |
| P               | 1.7       | REF       |
| R               | 1         | REF       |
| T               | 0.13      | REF       |
| A               | 3.6       | MIN       |
| G               | 3.5       | REF       |
| E               | 3.5       | REF       |

| Packaging Specifications |             |
|--------------------------|-------------|
| Package Kind:            | T&R         |
| Package Size:            | 7 in/180 mm |
| Package Quantity:        | 500         |

| General Information    |                    |
|------------------------|--------------------|
| Supplier:              | KEMET              |
| Application:           | General Purpose    |
| Part Type Description: | SMD, MnO2, Molded  |
| Construction:          | Standard Chip-MnO2 |
| Body Type:             | SMD Chip           |
| Footprint:             | 7343               |
| Weight:                | 652.04 mg          |
| RoHS:                  | Yes                |

| Specifications          |                    |
|-------------------------|--------------------|
| Capacitance:            | 10 uF              |
| Tolerance:              | +/-10%             |
| Voltage:                | 50 VDC (85C)       |
| Voltage:                | 33.5 VDC (125C)    |
| Temperature Range:      | -55/+125C          |
| Current/Ripple Current: | 486 mAmps (25C)    |
| Current/Ripple Current: | 437.4 mAmps (85C)  |
| Current/Ripple Current: | 194.4 mAmps (125C) |
| Resistance/ESR:         | 0.7 Ohms (100kHz)  |
| Failure Rate:           | N/A                |
| Leakage Current:        | 5 uA               |
| Dissipation Factor:     | 6%                 |