

Capacitor, film, Metallized Polypropylene, 2.2 uF, +/-20% Tol, -40/+110C, Safety: X2, 310 VAC, Lead Spacing=27.5 mm



General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	Safety: X2
Style:	Radial Box
Lead Form:	cut
Features:	Pulse
Approvals:	ENEC,UL,cUL,CQC
RoHS:	Yes

Dimensions (mm)		
Symbol	Dimension	Tolerance
L	32	+0.3
H	28	+0.1
T	14	+0.2
S	27.5	+/-0.4
LL	4	+2/-0
F	0.8	+/-0.05

Specifications	
Capacitance:	2.2 uF
Voltage:	630 VDC
Tolerance:	+/-20%
Voltage AC:	310 VAC
Rated Temperature:	110C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	0.1%
Insulation Resistance:	13.64 GOhm
Maximum dVdT:	150 v/us

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	352