

KEMET Part Number: C062K105K5X5CA
(CK06BX105K)

Capacitor, ceramic, 1 uF, +/-10% Tol, 50 V, BX, Lead Spacing=0.2"



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.366	+/-0.254
H	7.366	+/-0.254
T	2.286	+/-0.254
S	5.08	+/-0.762
LL	31.75	MIN
F	0.635	+0.102/-0.051

Notes:

-Lead Length Shown Is For Parts Supplied In Bulk, See Packaging Specifications For Lead Lengths When Not Provided In Bulk

General Information	
Supplier:	KEMET
Application:	MIL-PRF-11015
Temperature Coefficient:	BX
Body Type:	Radial Molded
Lead Type:	Wire Leads
Termination Type:	Tin-Lead (SnPb)
RoHS:	No

Specifications	
Capacitance:	1 uF
Voltage:	50 V
Tolerance:	+/-10%
Temperature Range:	-55/+125C
Failure Rate:	N/A
Testing:	MIL-PRF-11015
Dissipation Factor:	2.5%
Insulation Resistance:	1 GOhm
Dielectric Strength:	125 V

Packaging Specifications	
Package Kind:	Bulk
Package Type:	Bag
Package Quantity:	100