


Capacitor, aluminum, 1200 uF, +/-20% Tol, -40/+150C, 40 VDC@150C



Dimensions (mm)		
Symbol	Dimension	Tolerance
D	16	+/-0.5
L	26.5	+/-1
L1	33	MIN
LLPos	40	+/-2
LLNeg	40	+/-2
F	1	+/-0.03

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	125

General Information	
Supplier:	KEMET
Application:	150C
Part Type Description:	Vibration Resistant Extremely High Ripple Axial Aluminum Electrolytic
Lead Type:	Wire Leads
Weight:	8 g
RoHS:	Yes

Specifications	
Capacitance:	1200 uF
Voltage:	40 VDC
Tolerance:	+/-20%
Rated Temperature:	150C
Temperature Range:	-40/+150C
Life:	1500 Hrs
Leakage Current:	144 uA
Leakage Condition:	uAmps (5min 20C)
Resistance/ESR:	80 mOhms (100Hz 20C)
Resistance/ESR:	36 mOhms (100kHz 20C)
Resistance/ESR:	13 mOhms (5-100kHz 150C)
Current/Ripple Current:	16.6 Amps (5kHz 125C, With Heat Sink)
Current/Ripple Current:	10.5 Amps (5kHz 140C, With Heat Sink)
Current/Ripple Current:	4.7 Amps (5kHz 150C, Reduced Voltage And Heat Sink)
Current/Ripple Current:	5.8 Amps (5kHz 125C)
Current/Ripple Current:	7.4 Amps (>=5kHz 125C Reduced Voltage)
Miscellaneous:	Rated Voltage Measured At 125C

Statements of suitability for certain applications are based on our knowledge of typical operating conditions for such applications, but are not intended to constitute - and we specifically disclaim - any warranty concerning suitability for a specific customer application or use. This Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by us with reference to the use of our products is given gratis, and we assume no obligation or liability for the advice given or results obtained.