


**KEMET Part Number: T491C335K035AT**  
(B45196E6335K309)

Capacitor, Tantalum, SMD, MnO2, Molded, 3.3 uF, 6032, +/-10% Tol, 35 VDC (85C)



**Dimensions (mm)**

Symbol	Dimension	Tolerance
L	6	+/-0.3
W	3.2	+/-0.3
H	2.5	+/-0.3
F	2.2	+/-0.1
S	1.3	+/-0.3
B	0.5	+/-0.15
X	0.1	+/-0.1
P	0.9	REF
R	1	REF
T	0.13	REF
A	2.9	MIN
G	2.8	REF
E	2.4	REF

**Packaging Specifications**

Package Kind:	T&R
Package Size:	7 in/180 mm
Package Quantity:	500

**General Information**

Supplier:	KEMET
Application:	General Purpose
Part Type Description:	SMD, MnO2, Molded
Construction:	Standard Chip-MnO2
Body Type:	SMD Chip
Footprint:	6032
Weight:	224.48 mg
RoHS:	Yes

**Specifications**

Capacitance:	3.3 uF
Tolerance:	+/-10%
Voltage:	35 VDC (85C)
Voltage:	23.45 VDC (125C)
Temperature Range:	-55/+125C
Current/Ripple Current:	235 mAmps (25C)
Current/Ripple Current:	211.5 mAmps (85C)
Current/Ripple Current:	94 mAmps (125C)
Resistance/ESR:	2 Ohms (100kHz)
Failure Rate:	N/A
Leakage Current:	1.2 uA
Dissipation Factor:	6%